

G2-LAURA-W-P

~45° wide beam. Assembly with thinner white holder, installation tape and location pins.



SPECIFICATION:

Dimensions	21.6 x 21.6 mm
Height	13.1 mm
Fastening	tape, pin
ROHS compliant	yes ⓘ


LEDiL®

MATERIALS:

Component	Type	Material	Colour	Finish
LAURA-W	Single lens	PMMA	clear	
LAURA-LT-PIN-XP-HLD-WHT	Holder	PC	white	
ROSE-TAPE	Tape	Acrylic foam	black	


ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
CA13634_G2-LAURA-W-P » Box size: 450 x 260 x 160 mm	Single lens	1440	360	180



See also our general installation guide: www.ledil.com/installation_guide


OPTICAL RESULTS (MEASURED):





OPTICAL RESULTS (MEASURED):





LED XP-G
 FWHM / FWTM 46.0° / 65.0°
 Efficiency 91 %
 Peak intensity 1.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XP-G2
 FWHM / FWTM 47.0° / 71.0°
 Efficiency 87 %
 Peak intensity 1.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED XP-L HD
 FWHM / FWTM 49.0° / 76.0°
 Efficiency 85 %
 Peak intensity 1.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




OPTICAL RESULTS (MEASURED):





LED XT-E
FWHM / FWTM 43.0° / 69.0°
Efficiency 87 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED LUXEON 3030 2D (Round LES)
FWHM / FWTM 37.0° / 62.0°
Efficiency 86 %
Peak intensity 1.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:








LED LUXEON TX
FWHM / FWTM 42.0° / 67.0°
Efficiency 86 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NCSxx19A
FWHM / FWTM 41.0° / 66.0°
Efficiency 88 %
Peak intensity 1.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):

	LED NVSW219F		
FWHM / FWTM 48.0° / 76.0°			
Efficiency 91 %			
Peak intensity 1.2 cd/lm			
LEDs/each optic 1			
Light colour White			
Required components:			
	LED NVSxx19A		
FWHM / FWTM 41.0° / 67.0°			
Efficiency 87 %			
Peak intensity 1.7 cd/lm			
LEDs/each optic 1			
Light colour White			
Required components:			
	LED NVSxx19B/NVSxx19C		
FWHM / FWTM 41.0° / 68.0°			
Efficiency 84 %			
Peak intensity 1.7 cd/lm			
LEDs/each optic 1			
Light colour White			
Required components:			
 Opto Semiconductors	LED OSLON Square EC		
FWHM / FWTM 46.0° / 71.0°			
Efficiency 87 %			
Peak intensity 1.4 cd/lm			
LEDs/each optic 1			
Light colour White			
Required components:			

OPTICAL RESULTS (MEASURED):


SAMSUNG

LED LH351D
FWHM / FWTM 52.0° / 81.0°
Efficiency 92 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SEOUL SEMICONDUCTOR

LED Z5M3
FWHM / FWTM 43.0° / 72.0°
Efficiency 92 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):




LED	XHP35 HI
FWHM / FWTM	45.0° / 65.0°
Efficiency	93 %
Peak intensity	1.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XP-G3
FWHM / FWTM	50.0° / 68.0°
Efficiency	93 %
Peak intensity	1.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XQ-E HI
FWHM / FWTM	41.0° / 58.0°
Efficiency	94 %
Peak intensity	2.3 cd/lm
LEDs/each optic	1
Light colour	Red

Required components:



LED	XQ-E HI
FWHM / FWTM	46.0° / 60.0°
Efficiency	95 %
Peak intensity	1.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




OPTICAL RESULTS (SIMULATED):

OSRAM

Opto Semiconductors

LED	OSLON Black
FWHM / FWTM	41.0° / 55.0°
Efficiency	95 %
Peak intensity	2.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




OSRAM

Opto Semiconductors

LED	OSLON Black Flat (LUW HWQP)
FWHM / FWTM	34.0° / 54.0°
Efficiency	94 %
Peak intensity	2.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:





OSRAM

Opto Semiconductors

LED	OSLON Square Flat
FWHM / FWTM	41.0° / 59.0°
Efficiency	94 %
Peak intensity	2.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



OSRAM

Opto Semiconductors

LED	SFH 4770S
FWHM / FWTM	27.0° / 50.0°
Efficiency	93 %
LEDs/each optic	1
Light colour	White

Required components:

OPTICAL RESULTS (SIMULATED):



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)