




REV.	Q'TY	ECN. NO.	APR.	DATE




RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED METAL MASK T=0.12mm





▨ SMT SOLDER AREA
▩ NO PATTERN AND VIA HOLE IN HTIS AREA

NOTES:

- ELECTRICAL CHARACTERISTICS:
 - CURRENT RATING: 0.5 Amp. MAX.
 - VOLTAGE: 100V DC. MAX.
 - LOW LEVEL CONTACT RESISTANCE: 100 mOhms MAX. INITIALLY.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC MIN. FOR 1 MINUTE.
 - INSULATION RESISTANCE: (INITIAL) 1000MOhms MIN.. (FINAL) 100MOhms MIN.
BY APPLYING 500V DC ON MATED AND UNMATED CONNECTORS THROUGH MIL-STD-202, METHOD 302.
- MECHANICAL CHARACTERISTICS:
 - DURABILITY: 5000 CYCLES.
 - OPERATING TEMP. RANGE: -25°C TO 85°C.
[INCLUDING TERMINAL TEMP. RISE]
 - STORAGE TEMP.: -40°C TO 85°C.
- DIMENSIONS MARKED ∇ ARE MAJOR CHECKED DIMENSIONS.
- HARMFUL MATERIAL CONTROL PLEASE FOLLOW DOC. NO. "EPI12".
- QUANTITY OF PRODUCTS: 1400PCS/REEL



SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C4	RESERVED
C5	GND
C6	VPP
C7	I/O
C8	RESERVED



DIMENSION IN mm				厦门市辛译精密电子有限公司 Xiamen XinYi Xyecom Electronics Co.,Ltd	
TOLERANCE UNLESS OTHERWISE SPECIFIED				TITLE: 1.35H 7PIN PUSH PUSH MICRO SIM CARD CONNECTOR	
.X±0.35	X.*± 5'	APR.	Alex	DWG NO. SIM202-ZYB7AH1.35	
.XX±0.25	.X*± 3'	CHK.	Jack	PROJ. CUSTOMER DRAWING	
.XXX±0.15	.XX*± 1'	DRA.	Can	SIZE A4	SCALE 1:1 SHEET 1/1 REV. A