

## DAISY-7X1-BW

~80° batwing beam

### SPECIFICATION:

Dimensions	40.0 x 259.0 mm
Height	40 mm
ROHS compliant	yes ⓘ

### MATERIALS:

Component	Type	Material	Colour	Finish
C18806_DAISY-7X1-BW	Multi-lens	PMMA	clear	
C18409_DAISY-7X1-SHD-MET-MATT	Shade	PC	metal	matt
C18167_DAISY-7X1-SHD-MET	Shade	PC	metal	gloss
C17225_DAISY-7X1-SHD-WHT-MATT	Shade	PC	white	matt
C17051_DAISY-7X1-SHD-MATT	Shade	PC	black	matt
C16876_DAISY-7X1-SHD-WHT	Shade	PC	white	gloss
C16872_DAISY-7X1-SHD	Shade	PC	black	gloss



### ORDERING INFORMATION:


#### Quantities for one set:

Multi-lens	1
Shade	1



Component		Qty in box	MOQ	MPQ	Box weight (kg)
C18806_DAISY-7X1-BW » Box size: 400 x 300 x 300 mm	Multi-lens	312	312	24	5.7
C17225_DAISY-7X1-SHD-WHT-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.6
C16872_DAISY-7X1-SHD » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1
C18167_DAISY-7X1-SHD-MET » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
C16876_DAISY-7X1-SHD-WHT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.6
C18409_DAISY-7X1-SHD-MET-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
C17051_DAISY-7X1-SHD-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.3






See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)

### OPTICAL RESULTS (MEASURED):

#### TRIDONIC


LED LLE 20x280mm 750lm 827-865 LV MD ADV1  
FWHM / FWTM Asymmetric  
Efficiency 78 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 4  
Light colour Tunable White  
Required components:  
C16872\_DAISY-7X1-SHD




### OPTICAL RESULTS (SIMULATED):




LED LUXEON 2835 Line  
FWHM / FWTM 75.0 + 78.0° / 92.0 + 94.0°  
Efficiency 89 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 4  
Light colour White  
Required components:  
C16872\_DAISY-7X1-SHD




LED LinLED 280x20mm 1100lm 8x0 2C 42V Opt G1  
FWHM / FWTM 78.0° / 94.0°  
Efficiency 87 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:  
C16872\_DAISY-7X1-SHD



LED LinLED 280x20mm 1100lm 8x0 2C 42V Opt G1  
FWHM / FWTM 78.0° / 94.0°  
Efficiency 87 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:  
C17051\_DAISY-7X1-SHD-MATT




LED LinLED 280x20mm 1100lm 8x0 2C 42V Opt G1  
FWHM / FWTM 78.0° / 94.0°  
Efficiency 90 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 2  
Light colour White  
Required components:  
C16876\_DAISY-7X1-SHD-WHT



### OPTICAL RESULTS (SIMULATED):


#### MST Your solutions

LED LinLED 280x28mm 1100lm 8x0 2C 42V Opt G1  
 FWHM / FWTM 77.0° / 94.0°  
 Efficiency 90 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 4  
 Light colour White  
 Required components:  
 C17225\_DAISY-7X1-SHD-WHT-MATT




#### OSRAM Opto Semiconductors

LED Duris E 2835  
 FWHM / FWTM 76.0 + 79.0° / 92.0 + 96.0°  
 Efficiency 88 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 4  
 Light colour White  
 Required components:  
 C16872\_DAISY-7X1-SHD




#### OSRAM Opto Semiconductors

LED Duris E 2835  
 FWHM / FWTM 77.0° / 94.0°  
 Efficiency 88 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 4  
 Light colour White  
 Required components:  
 C17051\_DAISY-7X1-SHD-MATT



#### OSRAM Opto Semiconductors


LED Duris E 2835  
 FWHM / FWTM 77.0° / 94.0°  
 Efficiency 90 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 4  
 Light colour White  
 Required components:  
 C17225\_DAISY-7X1-SHD-WHT-MATT



### OPTICAL RESULTS (SIMULATED):


#### TRIDONIC

LED LLE 24x280mm 750lm 8x0 LVD ADV1  
FWHM / FWTM Asymmetric  
Efficiency 86 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 4  
Light colour White  
Required components:  
C17051\_DAISY-7X1-SHD-MATT



#### TRIDONIC

LED LLE 24x280mm 750lm 8x0 LVD ADV1  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 4  
Light colour White  
Required components:  
C17225\_DAISY-7X1-SHD-WHT-MATT





### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13  
FI-24240 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Salo, Finland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)