PRODUCT C17221_STRADELLA-8-HV-CSP-LN1

STRADELLA-8-HV-CSP-LN1

Beam for EN13201 M-class requirements with high poles or where road width is equal or less the pole height. Variant with improved creepage distance for high voltage circuit design.

SPECIFICATION:

Dimensions 50.0 x 50.0 mm Height 4.4 mm Fastening screw **ROHS** compliant yes 🕕



MATERIALS:

Component **Type** Material Colour **Finish** STRADELLA-8-HV-CSP-LN1 **PMMA** Multi-lens clear


ORDERING INFORMATION:

Box weight (kg) Component Qty in box MOQ MPQ C17221 STRADELLA-8-HV-CSP-LN1 800 160 160 5.6

» Box size: 480 x 280 x 300 mm



PRODUCT DATASHEET C17221_STRADELLA-8-HV-CSP-LN1




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo FastFlex LED 4x8up PR G5

FWHM / FWTM Asymmetric
Efficiency 96 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG

LED LH151B
FWHM / FWTM Asymmetric
Efficiency 93 %
Peak intensity 1.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



3/7

OPTICAL RESULTS (SIMULATED):



LED

XD16

FWHM / FWTM

Asymmetric 90 %

Efficiency Peak intensity


0.8 cd/lm

LEDs/each optic

Light colour

White

Required components:



MUMILEDS

LED

LUXEON CZ

FWHM / FWTM

Asymmetric

Efficiency


90 %

Peak intensity LEDs/each optic 0.8 cd/lm

Light colour

1 White

Required components:



LUMILEDS

LED

LUXEON HL2Z

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$

Asymmetric

Efficiency

91 %

Peak intensity

0.8 cd/lm


LEDs/each optic

1

Light colour

White

Required components:



MUMILEDS

LED Efficiency LUXEON HL2Z

FWHM / FWTM

Asymmetric

Peak intensity

76 % 0.4 cd/lm


LEDs/each optic

Light colour

White

Required components:

Protective plate, glass




PRODUCT DATASHEET C17221_STRADELLA-8-HV-CSP-LN1

OPTICAL RESULTS (SIMULATED):



LED NVSxE21A
FWHM / FWTM Asymmetric
Efficiency 91 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour White


Required components:



WNICHIA

LED NVSxE21A
FWHM / FWTM Asymmetric
Efficiency 76 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:


Protective plate, glass



OSRAM

Opto Semiconductors

LED OSCONIQ C 2424
FWHM / FWTM Asymmetric
Efficiency 91 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OSRAM

LED OSCONIQ C 2424
FWHM / FWTM Asymmetric
Efficiency 78 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White

Protective plate, glass

Required components:



5/7

PRODUCT DATASHEET C17221_STRADELLA-8-HV-CSP-LN1


OPTICAL RESULTS (SIMULATED):

Fortimo FastFlex LED 4x8up PR G5

FWHM / FWTM Asymmetric Efficiency 83 % Peak intensity 0.6 cd/lm LEDs/each optic Light colour White

Required components:

Protective plate, glass




SAMSUNG

LED LH151B FWHM / FWTM Asymmetric Efficiency 79 % Peak intensity 0.8 cd/lm LEDs/each optic 1

White Light colour Required components:

Protective plate, glass




SAMSUNG

LED LH181B FWHM / FWTM Asymmetric Efficiency 76 % Peak intensity 0.4 cd/lm LEDs/each optic 1

Light colour White Required components:

Protective plate, glass




SAMSUNG

LH181B FWHM / FWTM Asymmetric Efficiency 90 % Peak intensity 0.7 cd/lm LEDs/each optic White

Required components:

Light colour





PRODUCT DATASHEET C17221_STRADELLA-8-HV-CSP-LN1

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

7/7

www.ledil.com/ where_to_buy