

LISA-RS

~15° spot beam optimized for Golden Dragon

SPECIFICATION:

Dimensions	Ø 11.0 mm
Height	7.9 mm
Fastening	glue
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
LISA-O1-RS	Single lens	PMMA	clear	
LISA-O1-HLD	Holder	PC	white	



ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CP11626_LISA-RS	Single lens	10000	300	100	5.5
» Box size: 254 x 298 x 241 mm					



See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):


OSRAM
Opto Semiconductors

LED	Golden Dragon
FWHM / FWTM	12.0° / 31.0°
Efficiency	91 %
LEDs/each optic	1
Light colour	White
Required components:	


OPTICAL RESULTS (SIMULATED):





LED XHP35.2 HI
FWHM / FWTM 18.0° / 53.0°
Efficiency 76 %
Peak intensity 2.3 cd/Im
LEDs/each optic 1
Light colour White
Required components:




LED XP-G3
FWHM / FWTM 21.0° / 47.0°
Efficiency 85 %
Peak intensity 3.2 cd/Im
LEDs/each optic 1
Light colour White
Required components:



LED SST-10-IR-B90
FWHM / FWTM 17.0° / 37.0°
Efficiency 86 %
LEDs/each optic 1
Light colour IR
Required components:




LED NV4WB35AM
FWHM / FWTM 24.0° / 65.0°
Efficiency 80 %
Peak intensity 1.9 cd/Im
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):



LED NVSW519A
FWHM / FWTM 28.0° / 58.0°
Efficiency 85 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED NVSxx19B/NVSxx19C
FWHM / FWTM 19.0° / 44.0°
Efficiency 81 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




Opto Semiconductors

LED OSOLON SSL 150
FWHM / FWTM 13.0° / 28.0°
Efficiency 87 %
Peak intensity 7.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:



Opto Semiconductors

LED OSOLON SSL 150
FWHM / FWTM 12.0° / 28.0°
Efficiency 87 %
Peak intensity 7.7 cd/lm
LEDs/each optic 1
Light colour Red
Required components:





OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors

LED SFH 4727AS
FWHM / FWTM 17.0° / 49.0°
Efficiency 83 %
LEDs/each optic 1
Light colour IR
Required components:

Polar intensity graph



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)