

DSUB SV MA SSDP STR 25P PL3 GC SLK 4-40



Image is for illustration purposes only. Please refer to product description.

Part number	09 65 361 7713
Specification	DSUB SV MA SSDP STR 25P PL3 GC SLK 4-40
HARTING eCatalogue	https://b2b.harting.com/09653617713

Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Stamped Straight

Version

Termination method	Wave soldering termination
Gender	Male
Size	D-Sub 3
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	25
Termination length	3.7 mm
PCB fixing	With board locks
Locking type	Fixing flange with fitted screw lock 4-40 UNC

Technical characteristics

Distance between rows	2.84 mm
Contact spacing (termination side)	2.76 mm
Rated current	6.5 A
Clearance distance	≥1 mm
Creepage distance	≥1 mm



Pushing Performance
Since 1945

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	$\leq 0.4 \text{ Nm}$ Locking screw
Limiting temperature	$-55 \dots +125 \text{ }^{\circ}\text{C}$
Insertion force	$\leq 83 \text{ N}$
Withdrawal force	$\geq 7.8 \text{ N}$ $\leq 56 \text{ N}$
Performance level	3
Mating cycles	≥ 50
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ($175 \leq \text{CTI} < 400$)
PCB thickness	$\geq 1.6 \text{ mm}$
Installation height	6.2 mm
Hot plugging	No

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: Plated steel
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel



Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R26
------------------------------------	-----

Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079

Commercial data

Packaging size	100
Net weight	13.7 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140078581
ETIM	EC001136
eCl@ss	27440214 D-Sub coupler