# SERIES FPS

## 5D CARD AND MMC CONNECTOR - ONE ACTION LOCK TYPE

#### **SPECIFICATIONS**

 $\begin{tabular}{lll} Insulation Resistance: & 1,000M$\Omega$ min. at 500V DC \\ Withstanding Voltage: & 500V ACrms for 1 minute \\ Contact Resistance: & 100m$\Omega$ at 1m$A$ / 20m$V$ max. \\ \end{tabular}$ 

 Voltage Rating:
 5V DC

 Current Rating:
 0.5A max.

 Operating Temp. Range:
 -30°C to +85°C

Mating Cycles: 100


### MATERIALS AND FINISH


Insulator: LCP

Contact: Copper Alloy, Ni-Au

### **FEATURES**

- . Automatic locking function after insertion of SD card
- 2-point contact installation on all contact-terminals to ensure die-electric discontinuity prevention which may be caused by vibration and impact
- Zero sliding contact @100G shock (X Y Z direction)
- Metal shell cover with 4 GNDs (Solder tubs) to ensure EMI/ESD prevention performance
- RoHS2011/65/EU





Shell OND

Shell GND