

97 mm L x 61 mm W x 25 mm H (3.8"L x 2.4" W x 1.0"H)

UHF RAIN RFID Desktop Reader

The ThingMagic USBPro RFID Reader allows solutions developers to support applications that require desktop reading and writing of EPC Global Gen2 tags, as well as other protocols such as ISO18000-6B, IPx and AEI ATA (read only) through additional license. Based on ThingMagic's M6e-Micro module, the USBPro RFID Reader is controlled and powered by a host P or laptop through a USB interface and supports autonomous operation. The USBPro RFID Reader is compatible with ThingMagic's MercuryAPI application development tools, including Universal Reader Assistant, permitting rapid creation of solutions. USBPro supports a wide range of applications, including tag commissioning, manufacturing work in progress, document tracking, retail Point of Sale, and workflows for healthcare, events, and hospitality.

Ordering Information		
Reader	USB-6EP	
Development Kit	USB-6EP-DEVKIT	
Tag / Transponder Protocols		
RFID Protocol	EPC Gen2V2 ISO18000-63 standard ISO18000- 6B, IPx, AEI ATA (read only) are available through additional license	
Support		
RF Interface		
Antenna Ports	Internal antenna with an average gain of +1 dBi from 865-869MHz and 902-928MHz, External RP-SMA antenna connector	
RF Power Output	Separate read and write levels (into the antenna) are command-adjustable from -5 dBm to 30 dBm* (1W), +/- 1.0 dBm accuracy with +20dBm default	
Frequency	Pre-configured for the following regions: FCC 902-928,917.4-927,917.5-922.5 MHz (Americas) ETSI 865.6-867.6 MHz, 869.85 MHz (EU) TRAI 865- 867 MHz (India) KCC 917-920.8 MHz (Korea) ACMA 920-926 MHz (Australia) SRRC-MII 920-925 MHz (P. R. China) MIC 916.7-920.9 MHz (Japan) Open (Customizable) 865-869 and 902-928 MHz	
Data/Control Interface		
Physical	USB Micro-B connector, with removable six (6) foot cable with dual USB-A type plug	
Signaling	USB 2.0	
Input/Output	Two I/O command controlled LEDs and two I/O command queried switches	

Regulatory Information		
Regulatory	FCC 47 CFR Ch. 1 Part 15, Industrie Canada RSS-21 0, ETSI EN 302 208 v3.1.1 (RED 2014/53/EU)	
Safety	IEC 60950-1 (ed.2) US-17650-UL	
Power		
DC Power Required	DC Voltage: 4.5 to 5.5 VDC from USB cable DC Power: 6.2 W max	
	Supplied interface cable terminates in two	
	type-A plugs: one for power and signal, the second for additional power if needed	
Idle Power	0.35 W max at idle	
Consumption	(Power management modes can be used to reduce this to as little as 0.1 W)	
Environment		
Operating Temp.	-40°C to +60°C*	
Storage Temp.	-40°C to +85°C	
Architecture		
User Memory	16 kB	
Tag Buffer	200 tags	
Performance		
Tag Read Rate	50 tags/second	
Tag Read Distance	Up to 10 m (30 feet) with external antenna and up to 1.2 m (4 feet) depending on tag Sensitivity and orientation with internal Antenna with max RF power.	
Duty cycle restrictions based o ower >23dB	n temperature, tx	



Protocol



and 16-bit CRC

USA Office

phone:+1 315.701.0678 email: info@jadaktech.com web: jadaktech.com

European Office

phone:+49 89 31 707 100 email: info@jadaktech.com

Asia Pacific Office phone: +86 512.6283.7080 email: info@jadaktech.com

© 2022 Novanta Inc. and its affiliated companies. All rights reserved. Rev 04262022

Command-response protocol protected by length field

