

VICTORIA-IP-W-PC

~60° wide beam. Ingress protected version made from PC.

SPECIFICATION:

Dimensions	Ø 300.0 mm
Height	18.1 mm
Fastening	screw
Ingress protection classes	IP65, IP66, IP67
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
VICTORIA-W-PC	Multi-lens	PC	clear	
VICTORIA-O-RING	Seal	Silicone	milky	
VICTORIA-SEAL	Seal	Silicone	clear	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CS16981_VICTORIA-IP-W-PC	Multi-lens	34	34	34	10.2
» Box size: 343 x 343 x 298 mm					







OPTICAL RESULTS (MEASURED):





LED Victoria-PCB
FWHM / FWTM 59.0° / 85.0°
Efficiency 83 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:



SAMSUNG


LED HiLOM HCF0 (LH181B)
FWHM / FWTM 44.0° / 68.0°
Efficiency 89 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):




LED J Series 2835
FWHM / FWTM 62.0° / 78.0°
Efficiency 91 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED LUXEON 2835 Line
FWHM / FWTM 61.0° / 76.0°
Efficiency 90 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LUXEON 2835 Line
FWHM / FWTM 69.0° / 90.0°
Efficiency 89 %
Peak intensity 0.8 cd/lm
LEDs/each optic 2
Light colour White
Required components:




LED Duris E 2835
FWHM / FWTM 61.0° / 77.0°
Efficiency 91 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (SIMULATED):


SAMSUNG

LED LM28xB Series
 FWHM / FWTM 61.0° / 77.0°
 Efficiency 91 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




SAMSUNG


LED LM302D
 FWHM / FWTM 50.0° / 68.0°
 Efficiency 81 %
 Peak intensity 1.1 cd/lm
 LEDs/each optic 2
 Light colour White
 Required components:



LED SEOUL DC 3528
 FWHM / FWTM 70.0° / 90.0°
 Efficiency 93 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 2
 Light colour White
 Required components:



LED SEOUL DC 3528
 FWHM / FWTM 64.0° / 80.0°
 Efficiency 91 %
 Peak intensity 1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)