



Click [here](#) for the 3D model.

## Dimensions

D	65mm +/-0.5mm
L	247mm +/-2mm
W	18mm +/-1mm
S	28mm +/-1mm
W1	40mm +/-1mm

## Packaging Specifications

Mounting	Bolt - M12x16
Packaging	Bulk, Bag

## General Information

Series	C20A
Dielectric	Metallized Polypropylene
Style	Can
Features	Single Phase PFC
RoHS	With Exemptions
SCIP Number	2d92f699-4786-4192-9c9d-d5c4faebc1e6
Lead	Threaded Studs M10
AEC-Q200	No
Miscellaneous	Thermal Resistance = 6.2 C/W.
Notes	This part is Not For New Design. See part number C44PPGR5680RASK.

## Specifications

Capacitance	68 uF
Capacitance Tolerance	10%
Voltage AC	550 VAC
Voltage DC	1280 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
Insulation Resistance	10 MOhms
Max dV/dt	30 V/us
Resistance	1.7 mOhms (10kHz)
Ripple Current	55 Amps (10kHz 40°C)
Inductance	145 nH