

OLGA-M

~30° wide beam. Assembly with holder and installation tape.

SPECIFICATION:

Dimensions	Ø 32.0 mm
Height	19.1 mm
Fastening	tape, pin
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
OLGA-M	Single lens	PMMA	clear	
OLGA-HLD	Holder	PC	black	
SPUTNIK-TAPE3	Tape	Acrylic foam	black	



ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CA16128_OLGA-M	Single lens	792	132	66	9.8
» Box size: 476 x 273 x 292 mm					





See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):





LED XD16
FWHM / FWTM 26.0° / 48.0°
Efficiency 80 %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XHP35 HD
FWHM / FWTM 32.0° / 58.0°
Efficiency 80 %
Peak intensity 2.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED XHP35 HI
FWHM / FWTM 28.0° / 51.0°
Efficiency 84 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XHP50
FWHM / FWTM 32.0° / 60.0°
Efficiency 81 %
Peak intensity 2.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):





LED XHP50.2
FWHM / FWTM 31.0° / 58.0°
Efficiency 81 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED XHP70
FWHM / FWTM 33.0° / 63.0°
Efficiency 82 %
Peak intensity 2 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED XHP70.2
FWHM / FWTM 34.0° / 64.0°
Efficiency 81 %
Peak intensity 1.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XM-L
FWHM / FWTM 31.0° / 55.0°
Efficiency 83 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):





LED XM-L3
FWHM / FWTM 33.0° / 57.0°
Efficiency 81 %
Peak intensity 2.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XP-G2
FWHM / FWTM 30.0° / 53.0°
Efficiency 83 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED XP-G3
FWHM / FWTM 31.0° / 54.0°
Efficiency 82 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XP-L HI
FWHM / FWTM 28.0° / 50.0°
Efficiency 85 %
Peak intensity 3 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):





LED XP-L2
FWHM / FWTM 30.0° / 54.0°
Efficiency 81 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XQ-E HD
FWHM / FWTM 28.0° / 51.0°
Efficiency 76 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED XQ-E HI
FWHM / FWTM 27.0° / 49.0°
Efficiency 83 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XT-E
FWHM / FWTM 29.0° / 53.0°
Efficiency 79 %
Peak intensity 2.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):





LED LUXEON 5050 Round LES
FWHM / FWTM 27.0° / 52.0°
Efficiency 86 %
Peak intensity 3 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED LUXEON C
FWHM / FWTM 29.0° / 52.0°
Efficiency 76 %
Peak intensity 2.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LUXEON CZ
FWHM / FWTM 26.0° / 47.0°
Efficiency 85 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED LUXEON M/MX
FWHM / FWTM 31.0° / 59.0°
Efficiency 84 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (MEASURED):


LUMILEDS

LED LUXEON MZ
FWHM / FWTM 26.0° / 50.0°
Efficiency 85 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LUMILEDS

LED LUXEON Rebel ES
FWHM / FWTM 28.0° / 51.0°
Efficiency 83 %
Peak intensity 3 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LUMILEDS

LED LUXEON TX
FWHM / FWTM 29.0° / 51.0°
Efficiency 83 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LUMILEDS



LED LUXEON V
FWHM / FWTM 29.0° / 54.0°
Efficiency 82 %
Peak intensity 2.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (MEASURED):



LUMILEDS

LED LUXEON V
FWHM / FWTM 28.0° / 53.0°
Efficiency 82 %
Peak intensity 2.7 cd/m
LEDs/each optic 1
Light colour White
Required components:





LUMILEDS

LED LUXEON V2
FWHM / FWTM 29.0° / 51.0°
Efficiency 83 %
Peak intensity 2.9 cd/m
LEDs/each optic 1
Light colour White
Required components:





LUMILEDS

LED LUXEON Z
FWHM / FWTM 25.0° / 46.0°
Efficiency 85 %
Peak intensity 3.7 cd/m
LEDs/each optic 1
Light colour White
Required components:



LUMILEDS



LED LUXEON Z ES
FWHM / FWTM 27.0° / 49.0°
Efficiency 85 %
Peak intensity 3.3 cd/m
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):





LED NCSxE17A
FWHM / FWTM 23.0° / 44.0°
Efficiency 85 %
Peak intensity 4.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED NVSW219D
FWHM / FWTM 31.0° / 54.0°
Efficiency 83 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NVSW319B
FWHM / FWTM 34.0° / 56.0°
Efficiency 84 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED NVSxE21A
FWHM / FWTM 23.0° / 44.0°
Efficiency 85 %
Peak intensity 4.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):





LED NVSxx19B/NVSxx19C
 FWHM / FWTM 30.0° / 52.0°
 Efficiency 84 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED Duris S8
 FWHM / FWTM 27.0° / 53.0°
 Efficiency 85 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED OSCONIQ P 3737 (2W version)
 FWHM / FWTM 26.0° / 49.0°
 Efficiency 83 %
 Peak intensity 3.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED OSCONIQ P 3737 (3W version)
 FWHM / FWTM 28.0° / 51.0°
 Efficiency 84 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OPTICAL RESULTS (MEASURED):


OSRAM Opto Semiconductors

LED OSCONIQ P 7070
FWHM / FWTM 29.0° / 55.0°
Efficiency 83 %
Peak intensity 2.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OSRAM Opto Semiconductors

LED OSLON Black Flat (LUW HWQP)
FWHM / FWTM 24.0° / 45.0°
Efficiency 85 %
Peak intensity 3.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OSRAM Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 30.0° / 52.0°
Efficiency 84 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM Opto Semiconductors

LED OSLON Square EC
FWHM / FWTM 28.0° / 51.0°
Efficiency 81 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):

OSRAM

Opto Semiconductors



LED OSLON Square PC
FWHM / FWTM 29.0° / 52.0°
Efficiency 82 %
Peak intensity 2.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM

Opto Semiconductors



LED OSLON SSL 150
FWHM / FWTM 30.0° / 51.0°
Efficiency 82 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM

Opto Semiconductors



LED OSLON SSL 80
FWHM / FWTM 28.0° / 51.0°
Efficiency 82 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM

Opto Semiconductors



LED OSTAR Stage (S2WN)
FWHM / FWTM 26.0° / 50.0°
Efficiency 84 %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour RGBW
Required components:



OPTICAL RESULTS (MEASURED):



SAMSUNG

LED LH181A
FWHM / FWTM 22.0° / 44.0°
Efficiency 81 %
Peak intensity 4 cd/lm
LEDs/each optic 1
Light colour White
Required components:





SAMSUNG

LED LH181B
FWHM / FWTM 23.0° / 45.0°
Efficiency 85 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:





SAMSUNG

LED LH231B
FWHM / FWTM 24.0° / 47.0°
Efficiency 86 %
Peak intensity 3.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG



LED LH351B
FWHM / FWTM 30.0° / 53.0°
Efficiency 84 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (MEASURED):



SAMSUNG

LED LH351C
FWHM / FWTM 31.0° / 53.0°
Efficiency 85 %
Peak intensity 2.7 cd/m
LEDs/each optic 1
Light colour White
Required components:





SAMSUNG

LED LH351D
FWHM / FWTM 33.0° / 57.0°
Efficiency 83 %
Peak intensity 2.2 cd/m
LEDs/each optic 1
Light colour White
Required components:





SAMSUNG

LED LH508A
FWHM / FWTM 28.0° / 53.0°
Efficiency 85 %
Peak intensity 2.9 cd/m
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG



LED LM302A
FWHM / FWTM 25.0° / 48.0°
Efficiency 85 %
Peak intensity 3.4 cd/m
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LM561B
FWHM / FWTM 27.0° / 51.0°
Efficiency 85 %
Peak intensity 3.2 cd/m
LEDs/each optic 1
Light colour White
Required components:



LED WICOP 5050
FWHM / FWTM 33.0° / 60.0°
Efficiency 80 %
Peak intensity 2.1 cd/m
LEDs/each optic 1
Light colour White
Required components:




LED Z5M3
FWHM / FWTM 28.0° / 52.0°
Efficiency 82 %
Peak intensity 2.8 cd/m
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):




LED J Series 5050 Round LES
FWHM / FWTM 25.0° / 46.0°
Efficiency 92 %
Peak intensity 4.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED XHP50.3 HD
FWHM / FWTM 31.0 + 30.0° / 52.0°
Efficiency 83 %
Peak intensity 2.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED XHP50.3 HI
FWHM / FWTM 28.0° / 48.0°
Efficiency 95 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED XHP70.3 HD
FWHM / FWTM 33.0 + 32.0° / 58.0°
Efficiency 82 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):




LED XP-G2 HE
FWHM / FWTM 33.0° / 50.0°
Efficiency 89 %
Peak intensity 2.9 cd/Im
LEDs/each optic 1
Light colour White
Required components:




LED SST-20
FWHM / FWTM 26.0° / 42.0°
Efficiency 91 %
Peak intensity 4.5 cd/Im
LEDs/each optic 1
Light colour White
Required components:



LED SST-70X-WCS
FWHM / FWTM 30.0° / 50.0 + 48.0°
Efficiency 85 %
Peak intensity 3.1 cd/Im
LEDs/each optic 1
Light colour White
Required components:




LED COB S-Type (LES 7)
FWHM / FWTM 32.0° / 58.0°
Efficiency 91 %
Peak intensity 2.5 cd/Im
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):




LED COB T-Type
FWHM / FWTM 30.0° / 56.0°
Efficiency 91 %
Peak intensity 2.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED NCSxE17A
FWHM / FWTM 24.0° / 44.0°
Efficiency 88 %
Peak intensity 4.5 cd/lm
LEDs/each optic 4
Light colour White
Required components:



LED NFMW48xA
FWHM / FWTM 25.0° / 47.0°
Efficiency 92 %
Peak intensity 4.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED NV4WB35AM
FWHM / FWTM 25.0° / 44.0°
Efficiency 91 %
Peak intensity 4.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (SIMULATED):



LED NV4x144A
 FWHM / FWTM 31.0° / 54.0°
 Efficiency 86 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)