

PAIS-4-P/P BK - Test adapter



3032795

<https://www.phoenixcontact.com/us/products/3032795>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test adapter, Only use in UDK 4 MTK-P/P and UK 5-MTK-P/P, For 4 mm test plugs, number of positions: 1, color: black

Your advantages

- Reliable contacting of test plugs with a 4 mm diameter in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

Commercial data

Item number	3032795
Packing unit	10 pc
Sales key	BE19
Product key	BE2Z3X
GTIN	4055626011127
Weight per piece (including packing)	2.44 g
Weight per piece (excluding packing)	2.44 g
Customs tariff number	85366990
Country of origin	PL

PAIS-4-P/P BK - Test adapter

3032795

<https://www.phoenixcontact.com/us/products/3032795>



Technical data

Notes

General	Only use in UDK 4 MTK-P/P and UK 5-MTK-P/P
General	Do not plug in while the power is connected

Product properties

Product type	Test socket
Number of positions	1

Electrical properties

Maximum load current	10 A
Max. voltage	250 V

Connection data

Maximum load current	10 A
Connection method	Plug-in connection

Dimensions

Width	6 mm
Height	6.5 mm
Depth	53.3 mm

Material specifications

Color	black
Material	Copper alloy
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI)
---------------------------------	---

PAIS-4-P/P BK - Test adapter



3032795

<https://www.phoenixcontact.com/us/products/3032795>

	Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Connection method	Plug-in connection
-------------------	--------------------

PAIS-4-P/P BK - Test adapter

3032795

<https://www.phoenixcontact.com/us/products/3032795>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3032795>



EAC

Approval ID: RU C-DE.BL08.B.00511

PAIS-4-P/P BK - Test adapter



3032795

<https://www.phoenixcontact.com/us/products/3032795>

Classifications

ECLASS

ECLASS-11.0	27141148
ECLASS-12.0	27141148
ECLASS-13.0	27250304

ETIM

ETIM 9.0	EC002555
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PAIS-4-P/P BK - Test adapter



3032795

<https://www.phoenixcontact.com/us/products/3032795>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com