

Data sheet

2542.0 QKS 6, gelb



Crimp lug, Ring shape acc. to DIN 46237, Max. wire cross-section: 6 mm², Colour: Yellow

RAL: 1026

Business data

Article number	<u>2542.0</u>
Article name	QKS 6, gelb
GTIN (EAN)	4044211053352
Connector shape	Ring shape acc. to DIN 46237
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	1.59 g
Weight per piece (including packaging)	1.69 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Yellow

Data sheet

2542.0 QKS 6, gelb

Technical data

Dimensions

Length (input to middle of the ring hole)	22 mm
Width of ring	10 mm
Ring hole diameter	5.3 mm
Diameter of feed-in funnel	6.5 mm
Size DIN	A 5 - 6

Connection data

Wire cross-section, min.	4 mm ²
Wire cross-section, max.	6 mm ²
Wire cross-section AWG, min.	12
Wire cross-section AWG, max.	10

Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
Soldered	✓

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2542.0 QKS 6, gelb



Approvals

Standards and regulations

Standards / specifications

DIN EN 13599

Data sheet

2542.0 QKS 6, gelb



Media

Accessories
