

SCC 20 - Shield connection clamp



1019423

<https://www.phoenixcontact.com/us/products/1019423>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shield connection clamp, number of positions: 1, connection method: Spring-cage connection, mounting type: Neutral busbar, color: black

Your advantages

- Convenient single-handed installation
- Shield connection clamps for cable diameters up to 20 mm
- Modern spring technology protects against vibrations
- Low transfer impedance due to large-surface shield connection
- High corrosion resistance
- Unique marking surface for cable designations
- As components, it is not possible to certify shield connections in accordance with the requirements of the directive and standards for electrical equipment in potentially explosive areas. As such, shield connection clamps can be used in the Ex area even without an appropriate approval or marking.

Commercial data

Item number	1019423
Packing unit	10 pc
Sales key	BE75
Product key	BE7522
GTIN	4055626506043
Weight per piece (including packing)	38.77 g
Weight per piece (excluding packing)	38.77 g
Customs tariff number	85369010
Country of origin	CN

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



Technical data

Notes

General

Note	The shield connection clamps must not be used for strain relief of cables/conductors.
	Do not use for protective conductor connection.

Product properties

Product type	Shield connection clamp
Number of positions	1

Electrical properties

Maximum power dissipation for nominal condition	0 W
Contact resistance	< 0.001 Ω

Connection data

Stripping length	50 mm
------------------	-------

Dimensions

Width	24.7 mm
Height	41.4 mm
Depth	43.6 mm

Material specifications

Color	black
Flammability rating according to UL 94	V0
Insulating material group	CTI 600
Insulating material	PA 6.6
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Cable/line

External cable diameter	10 mm ... 20 mm
-------------------------	-----------------

SCC 20 - Shield connection clamp



1019423

<https://www.phoenixcontact.com/us/products/1019423>

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Spectrum	Service life test category 2, bogie-mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	$6.12 \text{ (m/s}^2\text{)}^2/\text{Hz}$
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Neutral busbar
---------------	----------------

SCC 20 - Shield connection clamp



1019423

<https://www.phoenixcontact.com/us/products/1019423>

Classifications

ECLASS

ECLASS-11.0	27141150
ECLASS-12.0	27141150
ECLASS-13.0	27250309

ETIM

ETIM 9.0	EC002020
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SCC 20 - Shield connection clamp



1019423

<https://www.phoenixcontact.com/us/products/1019423>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

SCC 20 - Shield connection clamp



1019423

<https://www.phoenixcontact.com/us/products/1019423>

Accessories

EML (10X4)R - Label

0815583

<https://www.phoenixcontact.com/us/products/0815583>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 10 x 4 mm, Number of individual labels: 10000

EML (10X7)R - Label

0816663

<https://www.phoenixcontact.com/us/products/0816663>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 10 x 7 mm, Number of individual labels: 10000

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



EML (15X6)R - Label

0803275

<https://www.phoenixcontact.com/us/products/0803275>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 15 x 6 mm, Number of individual labels: 2500

EML (15X9)R - Label

0815677

<https://www.phoenixcontact.com/us/products/0815677>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 15 x 9 mm, Number of individual labels: 2500

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



EML (16,5X5)R - Label

0816702

<https://www.phoenixcontact.com/us/products/0816702>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 16.6 x 5 mm, Number of individual labels: 2500

EML (16X7)R - Label

0818001

<https://www.phoenixcontact.com/us/products/0818001>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 16 x 7 mm, Number of individual labels: 10000

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



EML (17,5X8)R - Label

0816744

<https://www.phoenixcontact.com/us/products/0816744>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 17.5 x 8 mm, Number of individual labels: 2500

EML (19X6)R - Label

0816760

<https://www.phoenixcontact.com/us/products/0816760>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 19 x 6 mm, Number of individual labels: 2500

SCC 20 - Shield connection clamp

1019423


<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 SN 55MM 2X5,5 - Neutral busbar

5406304

<https://www.phoenixcontact.com/us/products/5406304>




Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 SN 300MM 2X5,2 - Neutral busbar

5406221

<https://www.phoenixcontact.com/us/products/5406221>



Neutral busbar

SCC 20 - Shield connection clamp

1019423


<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 SN 175MM - Neutral busbar

5406194

<https://www.phoenixcontact.com/us/products/5406194>




Neutral busbar

NLS-CU 3/10 SN 630MM - Neutral busbar

5406185

<https://www.phoenixcontact.com/us/products/5406185>



Neutral busbar, material: Copper, tin-plated

SCC 20 - Shield connection clamp

1019423


<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 SN 550MM - Neutral busbar

5406184

<https://www.phoenixcontact.com/us/products/5406184>




Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 SN 1550MM - Neutral busbar

5406170

<https://www.phoenixcontact.com/us/products/5406170>



Neutral busbar, material: Copper, tin-plated

SCC 20 - Shield connection clamp

1019423


<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 SN 93MM - Neutral busbar

5406159

<https://www.phoenixcontact.com/us/products/5406159>




Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 16.31.19.040-AA - Neutral busbar

5405865

<https://www.phoenixcontact.com/us/products/5405865>



Neutral busbar, material: Copper, tin-plated

SCC 20 - Shield connection clamp

1019423


<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 95MM ZG.160452 - Neutral busbar

5405857

<https://www.phoenixcontact.com/us/products/5405857>




Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 58MM ZG.155646 - Neutral busbar

5405855

<https://www.phoenixcontact.com/us/products/5405855>



Neutral busbar, material: Copper, tin-plated

SCC 20 - Shield connection clamp

1019423


<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 SN 90MM LANG - Neutral busbar

5405836

<https://www.phoenixcontact.com/us/products/5405836>




Neutral busbar, material: Copper, tin-plated

NLS-CU 3/10 245MM LG - Neutral busbar

5405831

<https://www.phoenixcontact.com/us/products/5405831>



Neutral busbar, material: Copper, tin-plated

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



NLS 3/10 AV 134/134 - Neutral busbar

3062870

<https://www.phoenixcontact.com/us/products/3062870>




Angled rail for holding the C-NBB busbar connector

NLS-CU 3/10 SN 150MM 2X3,5 - Neutral busbar

1044718

<https://www.phoenixcontact.com/us/products/1044718>



PEN conductor busbar, 3 mm x 10 mm

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 220MM 4X4,5 1XM4 - Neutral busbar

1013677

<https://www.phoenixcontact.com/us/products/1013677>



PEN conductor busbar, 3 mm x 10 mm

NLS-CU 3/10 SN 1000MM - Neutral busbar

0402174

<https://www.phoenixcontact.com/us/products/0402174>



Neutral busbar, DIN VDE 0611-4: 1991-02, material: Copper, tin-plated, color: silver

SCC 20 - Shield connection clamp

1019423

<https://www.phoenixcontact.com/us/products/1019423>



NLS-CU 3/10 SN 2000MM - Neutral busbar

0402006

<https://www.phoenixcontact.com/us/products/0402006>



Neutral busbar, DIN VDE 0611-4: 1991-02, material: Copper, tin-plated, color: silver

EMC SET SKH 134/134 - Shield connection clamp

3213247

<https://www.phoenixcontact.com/us/products/3213247>



Shield terminal set consisting of: C-NBB busbar connector, NLS 3/10 AV 134/134 angled rail, and AB-SKH shield terminal bracket

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com