# **Product data sheet**

Specification





# Thermal overload relay, Easy TeSys DPER, 0.1-0.16A, class 10

DPER01

#### Main

Range	Easy TeSys
Product Name	Easy TeSys DPER
Product Or Component Type	Thermal overload relay
Device Short Name	DPER
Relay Application	Overload protection
Product Compatibility	Contactor DPE09-38
Thermal Protection Adjustment Range	0.10.16 A
Thermal Overload Class	Class 10 IEC 60947-4-1
[Ui] Rated Insulation Voltage	Power circuit 600 V cUL Power circuit 690 V IEC 60947-4-1

## Complementary

<del></del>	
Network Type	DC
	AC
Network Frequency	0400 Hz
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	3 A 120 V AC-15 signalling circuit
	0.22 A 125 V DC-13 signalling circuit
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Protection Type	BS fuse 5 A control circuit
	GB2 circuit breaker 5 A control circuit
	GG fuse 5 A control circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz power circuit IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV
Surge Withstand	6 kV IEC 60801-5
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1
Control Type	Red push-button stop Blue push-button reset
Mounting Support	Separate, with specific accessories Under contactor

Connections - Terminals	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible without cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) solid without cable end Power circuit screw clamp terminals 1 0.000.01 in² (1.56 mm²) flexible without cable end Power circuit screw clamp terminals 1 0.000.01 in² (14 mm²) flexible with cable end Power circuit screw clamp terminals 1 0.000.01 in² (16 mm²) solid without cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals
Height	2.60 in (66 mm)
Width	1.77 in (45 mm)
Depth	2.76 in (70 mm)
Net Weight	0.27 lb(US) (0.124 kg)

## **Environment**

Ip Degree Of Protection	IP20 IEC 60529
Protective Treatment	TH IEC 60068
Temperature Compensation	-4140 °F (-2060 °C)
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) without derating IEC 60947-4-1
Ambient Air Temperature For Storage	-76158 °F (-6070 °C)
Shock Resistance	15 gn 11 ms IEC 60068-2-7
Vibration Resistance	6 gn on plate IEC 60068-2-6
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CUL
Product Certifications	dil

## **Packing Units**

PCE
1
3.50 in (8.89 cm)
1.90 in (4.826 cm)
3.00 in (7.62 cm)
4.80 oz (136.079 g)
S02
24
5.91 in (15 cm)
11.81 in (30 cm)
15.75 in (40 cm)
7.84 lb(US) (3.556 kg)
P06
384

Package 3 Height	30.31 in (77 cm)
Package 3 Width	23.62 in (60 cm)
Package 3 Length	31.50 in (80 cm)
Package 3 Weight	155.00 lb(US) (70.308 kg)

# Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information