# A Tallysman Accutenna® TW3440/TW3442 GPS/GLONASS 40dB Timing Antenna

The TW3440/TW3442 employs Tallysman's unique Accutenna technology, covering the GPS L1, GLONASS L1, and SBAS (WAAS, EGNOS & MSAS) frequency bands (1574 to 1606 MHz). They are especially designed for timing, mobile, precision and military applications. They provide truly circular response over the antenna's entire bandwidth thereby producing superior multipath signal rejection.

The TW3440/TW3442 each feature a highly circular dual-feed

wideband patch element, with a three stage This configuration Low Noise Amplifier. provides excellent axial ratio that is constant across the full frequency band. An optional tight pre-filter is available with part number TW3442 to protect against saturation by high level sub-harmonics and L-Band signals.

The TW3440/TW3442 is housed in a permanent mount industrial-grade weatherproof enclosure, and is available with a wide

variety of connectors. The antenna is available with either a flat or a conical radome. Conical radomes are recommended for permanent locations to ward off birds and shed ice / snow.

### **Applications**

Tallysman

- GPS / GLONASS Long cable Mobile/fixed Installations
- High Accuracy & Mission Critical Global Positioning •
- Precision Agriculture, Mining & Construction
- Military & Security •
- Law Enforcement & Public Safety

#### Features

- Great axial ratio: 1 dB typ. •
- High gain LNA: 40 dB min. •
- Low noise LNA: 1dB/3.5dB typ TW3440/TW3442
- Available sharp pre-filter (TW3442)
- Low current: 19 mA typ.
- Wide supply voltage: 2.5 to 16 VDC
- IP67 weather proof housing
- Available conical radome (Timing Apps)

### **Benefits**

14.2

- Excellent circular polarisation •
- Long Cable Runs •
- Excellent signal to noise ratio
- Excellent multipath rejection
- Exceptional out-of-band rejection (TW3442) •
- Increased system accuracy
- Ideal for harsh environments
- **RoHS and REACH compliant** •



4.3

Shown with low profile radome,

conical radome also available

## When **precision** matters..."

**F** 

# TW3440/TW3442 GPS/GLONASS 40dB Timing Antenna

**Specifications** Vcc = 3V, over full bandwidth, T=25°C

### Antenna

**Fallysman** 

Architecture 1 dB Bandwidth Antenna Gain (with 100mm ground plane) Axial Ratio (over full bandwidth)

#### Electrical

Architecture

Filtered LNA Frequency Bandwidth Polarization LNA Gain1575.42 to 1606 MHz Gain flatness Group Delay (TW3442 w/o cable) Out-of-Band Rejection <1500 MHz <1550 MHz >1640 MHz

VSWR (at LNA output) Noise Figure Supply Voltage Range (over coaxial cable) Supply Current ESD Circuit Protection

### Mechanicals & Environmental

Mechanical Size Operating Temp. Range Enclosure Weight Attachment Method Environmental Shock Vibration Salt Spray Dual, Quadrature Feeds 32 MHz 4.25 dBic 1 dB typ., 3 dB max.

TW3440: One LNA per feed ->Combiner ->SAW -> 2-Stage LNA TW3442: (SAW-> LNA) per feed ->Combiner -> SAW -> 2 Stage LNA,

1574 to 1606 MHz RHCP TW3440: 39 dB min., TW3442: 37dB min +/- 2 dB, 1575 to 1606 MHz 33.5nS @ 1575.42MHz 31.4nS @ 1590MHz 44.7nS @ 1606MHz >32 dB (TW3440) >50dB (TW3442) >25 dB >50dB >35 dB >70dB <1.5:1 typ. 1.8:1 max. 1 dB typ. TW3440 3.5dB typ. TW3442 2.5 to 16 VDC (12VDC recommended maximum) 19 mA (typ) 15 KV air discharge

> 66.5 mm dia. x 21 mm H -70 to +85 °C Radome: EXL9330 , Base: Zamak White Metal 135 g Permanent ¾" (19mm) through hole mount IP69k (5,000 psi), RoHS, REACH and RED compliant Vertical axis: 50 G, other axes: 30 G 3 axis, sweep = 15 min, 10 to 200 Hz sweep: 3 G MIL-STD-801F Section 509.4

### **Ordering Information**

TW3440 - GPS/GLONASS Antenna

33-3440-xx-yy-zzzz

TW3442 – 33-3442-xx-yy-zzzz

Where xx = connector type, yy = shape and colour of radome, and zzzz = cable length in mm (where applicable)

Please refer to the Ordering Guide <u>http://www.tallysman.com/wp-content/uploads/Current-Ordering-Guide.pdf)</u> for the current and complete list of available radomes and connectors.



Tel +1 613 591 3131

36 Steacie Drive, Ottawa ON K2K 2A9 Canada Fax 613 591 3121 <u>sales@tallysman.com</u>

The information provided herein is intended as a guide only and is subject to change without notice. This document is not to be regarded as a guarantee of performance. Tallysman Wireless Inc. hereby disclaims any or all warranties and liabilities of any kind. © 2010 Tallysman Wireless Inc. All rights reserved. Rev 5.3