

ATGBICS Universally Coded MSA Compliant Transceiver CWDM SFP
1000Base (120km, SMF, LC, 1530nm)

Brand : ATGBICS

Product code: CWDM-SFP-1G-1530-120-MSA-AT

Product name : Universally Coded MSA Compliant Transceiver CWDM SFP 1000Base (120km, SMF, LC, 1530nm)



ATGBICS Universally Coded MSA Compliant Transceiver CWDM SFP 1000Base (120km, SMF, LC, 1530nm)

ATGBICS Universally Coded MSA Compliant Transceiver CWDM SFP 1000Base (120km, SMF, LC, 1530nm):

ATGBICS Universally Coded MSA Network Transceivers are specifically designed for use in ‘open standard’ platforms. Unlike some OEMs such as Cisco and HP, other network equipment manufacturers do not have specific firmware coding requirements for compatibility with their brand of networking equipment. This form of ‘open coding’ or ‘generic coding’ network infrastructure supports versatile purchasing options of network transceivers. Our plug and play Universally Coded Transceivers are also ideal for clients building their own bespoke infrastructure. Our product meets all Multi-Source Agreement (MSA) standards for this form factor and are uniquely serialised for full date code and BOM traceability. We proudly offer a compatibility guarantee and lifetime replacement warranty

Performance		Features	
SFP transceiver type *	Fiber optic	Certification	CE, FCC, RoHS
Maximum data transfer rate *	1000 Mbit/s	Power	
Interface type *	SFP	Input voltage	3.3 V
Single-mode fiber (SMF) supported	✓	Maximum voltage	3.5 V
Multi-mode fiber (MMF) supported	✗	Power consumption (typical)	1 W
Fiber optic connector	LC	Operational conditions	
SFP transceiver standard	CWDM	Maximum operating temperature	70 °C
Maximum transfer distance	120000 m	Operating temperature (T-T)	0 - 70 °C
Wavelength	1530 nm	Storage temperature (T-T)	-40 - 85 °C
Coarse Wavelength Division Multiplexing (CWDM)	✓	Operating relative humidity (H-H)	0 - 95%
Ethernet LAN	✓	Storage relative humidity (H-H)	0 - 95%
Ethernet interface type	Gigabit Ethernet	Weight & dimensions	
Digital Diagnostics Monitoring (DDM)	✓	Width	13.4 mm
Features		Depth	56.5 mm
Product colour	Silver	Height	8.5 mm
Housing material	Metal	Weight	20 g
Plug and Play	✓	Packaging data	
Hot-swap	✓	Number of products included	1 pc(s)
Easy to install	✓	Package type	Blister
Country of origin	United Kingdom	Technical details	
Brand compatibility	MSA Compliant	Sustainability compliance	✓
		Sustainability certificates	RoHS, Federal Communications Commission (FCC), CE, REACH
		Doesn't contain	Lead



5056468774767

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date