

LSI Computer Systems, Inc. 1235 Walt Whitman Road, Melville, NY 11747 (631) 271-0400 FAX (631) 271-0405

TOUCH CONTROL HALOGEN LAMP DIMMER

FEATURES:

- Touch or pushbutton control of high-voltage lamps and *transformer-coupled low-voltage halogen lamps
- *Magnetic Transformers and most Electronic Transformers
- Automatic Safety Shutdown
- · Three operating modes
- · Extension input for remote activation
- 50Hz/60Hz AC line frequency
- +5V Power Supply (VDD -VSS)
- LS7634, LS7635 (DIP); LS7634-S, LS7635-S (SOIC); LS7634FO, LS7635FO (DIP);
- LS7634FO-S, LS7635FO-S (SOIC)
- See Figure 1 -

APPLICATIONS:

Electronic dimmers for wall switch control of ceiling mounted lighting, foot switch control of large floor lamps and hand switch control of table lamps.

BACKGROUND AND GENERAL DESCRIPTION:

A typical electronic dimmer may not operate properly with the inductive load encountered when driving a transformer-coupled low-voltage halogen lamp. The inductive load can cause a phenomenon called half-waving, wherein the triac fires in alternate half-cycles only, which may lead to the thermal destruction of the load transformer. The problems encountered in driving an inductive load are addressed by the LS7634/LS7635 family of CMOS ICs as follows:

1. Delayed triac cut-off.

When a trigger pulse is due to occur at a conduction angle which coincides with the on-state of the triac, the trigger pulse is delayed until the triac has turned off. This eliminates the underlying cause of half-waving.

2. Delayed triac turn-on and safety shutdown

With inductive loads, the holding current needed to maintain the triac On-State, may seriously lag behind the gate trigger signal causing the triac to turn off prematurely. If the frequency of occurrences of the delayed turn-on exceeds a preset threshold, a shutdown is initiated by turning off the triac trigger pulses. The safety-shutdown threshold value is accumulated in a 4-bit Up/Down counter. The count increments for every occurrence of delayed turn-on and decrements once every 8 SYNC pulses (AC line cycles). The counter will not decrement below zero. If the count reaches 15, the safety-shut-down is effected.

PIN ASSIGNMENT - TOP VIEW

October 2008



INPUT/OUTPUT DESCRIPTION:

VDD (Pin 1) Supply voltage positive terminal.

Vss (Pin 7) Supply voltage negative terminal.

MODE (Pin 2) - See Table 1

All variations of LS7634 and LS7635 can operate in 3 different modes. The 3-state MODE input selects the operating modes: Vss = Mode 0; Float = Mode 1; VDD = Mode 2

SYNC (Pin 4) - See Figure 6

The AC line frequency is applied to this input. All internal timings are synchronized to the AC. The Load On/Off status information is also derived from this input.

SENS (Pin 5) - See Table 1

A Logic 0 applied to this input alters the TRIG output either by turning it on, turning it off or by changing its conduction angle. Specifically which action takes place is dependent on the type of activation of the SENS input, namely SHORT or LONG touch and the prior state of TRIG output.

EXT (Pin 6)

Same functionality as the SENS input, except that a Logic 1 is the active level at this input. EXT input is intended to be operated from a remote site with long cable connection, when noise can be expected. The sampling method used at this input makes it less sensitive to noise.

TRIG (Pin 8)

The TRIG output is a low level pulse occurring once every halfcycle of the AC and is intended to drive the gate of a triac in series with the load. The conduction angle, \emptyset , of the TRIG pulse can be varied by means of LONG and SHORT touches at either the SENS or the EXT input.

Test (Pin 3) For factory use only.

The differences among all versions of LS7634 and LS7635 are: LS7634 (LS7634FO)____

Upon power-up, the TRIG output is Off.

(Upon power-up, the $\overline{\text{TRIG}}$ output is On at maximum conduction angle.) When a LONG touch is applied, the dimming direction automatically reverses whenever maximum or minimum conduction angles are reached.

LS7635 (LS7635FO)

Upon power-up, the TRIG output is Off.

(Upon power-up, the TRIG output is On at maximum conduction angle.) When a LONG touch is applied, the dimming stops whenever maximum or minimum conduction angles are reached. In order to change dimming levels from maximum or minimum, LONG touch must be removed and reapplied. The purpose of this feature is to allow the user to positively locate maximum and minimum conduction angles.

LS7635 NOTE:

If the User applies a LONG Touch when the TRIG Conduction Angle is within a "few" degrees of Maximum or Minimum, the TRIG Conduction Angle can move to Maximum or Minimum and stop without the User being able to observe a change in brightness. There-fore, the User should be instructed that if no change in brightness is observed in response to a LONG Touch, the LONG Touch should be re moved and reapplied in order to produce a change in brightness.

MODE	SHORT TOUCH			DIMMING				
	PRE-TOUCH Ø	POST-TOUCH Ø	PRE-TOUCH Ø	POST-TOUCH Ø	(Note 5)			
Γ	OFF	MAX(Note 1)	OFF/MIN	Varies up from MIN	N/A			
0	ON	OFF	MAX	Varies down from MAX	N/A			
			INTERMEDIATE	Varies from INTERMEDIATE	NO			
	OFF	MEMORY	OFF	Varies from memory (Notes 2, 3,4)	YES			
1		(Notes 2, 3)	MIN	Varies up from MIN	N/A			
	ON	OFF	MAX	Varies down from MAX	N/A			
			INTERMEDIATE	Varies from INTERMEDIATE	YES			
	OFF	MAX (Note 1)	OFF/MIN	Varies up from MIN	N/A			
2	ON	OFF	MAX	Varies down from MAX	N/A			
			INTERMEDIATE	Varies from INTERMEDIATE	YES			
Note Note	2: A soft turn-on is	produced by slewing produced by slewing the memory value is	up ø, from minimun		3.33ms (60Hz).			
Note				d prior to the current off-state.				
Note				n to memory upon which the dimming is sta	arted.			
Note		NO = Dimming direction does not reverse from prior dimming direction.						
				g direction. N/A = Does not apply.				

PARAMETER DC supply voltage	SYMBOL Vdd - Vss	VALUE +7	UNIT V
Any input voltage	Vin	Vss - 0.3 to VDD + 0.3	V
Operating temperature	ТА	0 to +90	°C
Storage temperature	Тѕтс	-65 to +150	°C

DC ELECTRICAL CHARACTERISTICS:

(TA = +25°C, all voltages referenced to Vss. VDD = +5V unless otherwise noted.)

PARAMETER	SYMBOL	MIN	ТҮР	МАХ	UNIT	CONDITION
Supply voltage Supply current	VDD IDD	4.5 -	5.0 300	5.5 400	V µA	- Output unloaded VDD = 5.5V
SYNC Lo	VISL	-	-	2.1	V	-
SYNC Hi	Vish	2.9	-	-	V	-
EXT, SENS Lo	VIEL	-	-	1.5	V	-
EXT, SENS Hi	VIEH	3.5	-	-	V	-
TRIG Lo	Vol	-	0.2	-	V	-
TRIG Hi	Vон	-	5.0	-	V	-
TRIG Sink Current	ITSNK	35	-	-	mA	VOTRIG = 2.5V

TIMING CHARACTERISTICS	(See Figures 2, 3 and 4):
------------------------	---------------------------

PARAMETER	SYMBOL	MIN	TYP	MAX	UNI T	CONDITION
SYNC Frequency	fs	40	-	70	Hz	-
SHORT Touch	Tsi	42	-	333	ms	60Hz
	Tsi	50	-	400	ms	50Hz
LONG Touch	TS2	342	-	infinite	ms	60Hz
	TS2	410	-	infinite	ms	50Hz
TRIG pulse width (see Note 5)	Tw	-	130	-	μs	60Hz
	Tw	-	156	-	μs	50Hz
Conduction Angle	Ø	50	-	154	deg	-
ø incremental steps (Note 1)	Ø	-	1.4	-	deg	-
Soft-on slew rate	Ss	-	1.4	-	deg/8.33ms	60Hz
	Ss	-	1.4	-	deg/10ms	50Hz
A0 to A1/A2 to A0 slew rate	SAA	-	1.4	-	deg/33.3ms	60Hz
(Note 2)	SAA	-	1.4	-	deg/40ms	50Hz
A1 to B1/B2 to A2 slew rate	SBA	-	1.4	-	deg/66.7ms	60Hz
(Note 3)	SBA	-	1.4	-	deg/80ms	50Hz
B1 to B2 delay	Твd	-	500	-	ms	60Hz
(Note 4)	Твd	-	600	-	ms	50Hz

Note 1: Total number of steps = 77.

Note 2: Number of steps from A0 to A1, or A2 to A0 = 55.

Note 3: Number of steps from A1 to B1 or B2 to A2 = 21.

Note 4: ø is at minimum between B1 and B2. TBD is applicable for LS7634 only.

For LS7635 when minimum ø is reached, dimming direction reverses only if the LONG Touch is terminated and reapplied. Note 5: Tw = 488us (60Hz), 586us (50Hz) available. Contact factory for details.



