

BRIGHT LED ELECTRONICS CORP.

BPD-BQDA38V-FZ04

END- LOOK PACKAGE PIN PHOTO DIODE

Features

- 1. Wide receiving angle
- 2. Linear response vs. irradiance
- 3. Fast switching time
- 4. End-looking Package ideal for space limited applications
- 5. Lens Appearance: Black
- 6. This product doesn't contain restriction substance, comply RoHS standard

Description

The BPD-BQDA38V-FZ04 device consists of a PIN silicon photodiode molded in a black epoxy package which allows spectral response infrared light wavelengths. The wide receiving angle provides relatively even reception over a large area. The end-looking package is designed for easy PC board mounting. This photodiode is mechanically and spectrally matched to BRIGHT's GaAs and GaAlAs series of infrared emitting diodes.

● Absolute Maximum Ratings(Ta=25°C)



4. Specifications are subject to change without notice

Parameter	Maximum Rating	Unit	
Power Dissipation	100	mW	
Reverse Breakdown Voltage	60V		
Operating Temperature	-40°C~+85°C		
Storage Temperature Range	-45°C~+85°C		
Lead Soldering Temperature	260° C for 5 seconds		

BRIGHT LED ELECTRONICS CORP.

BPD-BQDA38V-FZ04

• Electrical Characteristics (TA=25°C unless otherwise noted)

PARAMETER	SYM BOL	MIN	ТҮР	MAX	UNITS	TEST CONDITIONS
Reverse Light Current	١L	-	90		uA	V _R =5V.Ee=1mW/cm ²
Reverse Dark Current	I _D	-	-	100	nA	V _R =10V.Ee=0 mW/cm ²
Reverse Break down Voltage	$V_{(BR)}$	35	-	-	-	Ι _R =100μΑ
Forward Voltage	V _F	-	-	1.3	V	I _F =10mA
Total Capacitance	CT	-	9	-	PF	V _R =5V.Ee=0,f=1.0MHZ
Rise Time/ Fall Time	tr/tf	-	50	-	ns	V _R =20V,λ=940nm.RL=50Ω

• Typical Optical-Electrical Characteristic Curves



























Dip Soldering



- 1. Please avoid any external stress applied to the lead-frames and epoxy while the LEDs are at high temperature, especially during soldering
- 2. DIP soldering and hand soldering should not be done more than one time.
- 3. After soldering, avoid the epoxy lens from mechanical shock or vibration until the LEDs are back to room temperature.
- 4. Avoid rapid cooling during temperature ramp-down process
- 5. Although the soldering condition is recommended above,

soldering at the lowest possible temperature is feasible for the LEDs

IRON Soldering

- A: Max: 350℃ Within 3 sec. One time only.
- B: The products of 3mm without flange, welding condition of flat plate PCB Max: 350℃ Within 2 sec. One time only





• Tapping and packaging specifications(Units: mm)



• Packaging Bag Dimensions



Notes:

- $1 \smallsetminus 500 \text{pcs}$ per bag,5Kpcs per box.
- 2 · All dimensions are in millimeters(inches).
- 3 · Specifications are subject to change without notice.



Photodiode Specification

(Commodity: Photodiode

(Collector Current Bin Limits (IF=24mA Vce =5V)

BIN CODE	Min.(uA)	Max.(uA)
3	53	64
4	64	77
5	77	92
6	92	110
7	110	132

NOTES: Tolerance of measurement of Reverse Light Current $:\pm 15\%$