





技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩, 缺陷, 裂纹等现象.
2. 温度范围:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
3. 额定电压: 150V AC/DC.
4. 额定电流: 1.0A AC/DC(AWG#28).
5. 接触电阻:  $\leq 20\text{m}\Omega$ (Initial) per contact,  $\leq 40\text{m}\Omega$  Change allowed.
6. 绝缘电阻:  $\geq 500\text{M}\Omega$ .
7. 耐电压: 500V AC (Minute)

型号	CKT	A	B
WAFER-DF1.25-10PLB-GYR	2*5	10.50	5.00
WAFER-DF1.25-12PLB-GYR	2*6	11.75	6.25
WAFER-DF1.25-14PLB-GYR	2*7	13.00	7.50
WAFER-DF1.25-16PLB-GYR	2*8	14.25	8.75
WAFER-DF1.25-18PLB-GYR	2*9	15.50	10.00
WAFER-DF1.25-20PLB-GYR	2*10	16.75	11.25
.....	.....	.....	.....
WAFER-DF1.25-50PLB-GYR	2*25	$(25*1.25)+4.25$	$(25*1.25)-1.25$



PCB.WELDING DRAWING (TOLERANCE:±0.05)



4	1.25A型双排立式吸盖	LCP UL94V-0 本色
3	1.25A型双排立式芯芯	PA6T UL94V-0 本色
2	1.25A型双排立式焊片	黄铜/表面镀锡80u" Min, 镀镍30u"Min
1	1.25A型双排立式端子	黄铜/表面镀锡80u" Min, 镀镍30u"Min
序号	名称	数量

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 1.25 Pitch A型(DF13)双排立式带柱业务图
DECIMALS:	ANGLES:		PAR WAFER-DF1.25-NPLB-GYR
X.X±0.30	X.*±5°		DWN
X.XX±0.25	X.X*±1°		CHKD
X.XXX±0.15		APVD	SCALE:A UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1 REV:A