

Programmable Quad Buffer with Pre and Post Scaler Dividers

October 1993

Features

- Sine Wave Speedometer Input
- Input Limiting $\pm 0.25V$ to $\pm 100V$ (with $40k\Omega$)
- Over Voltage Protection
- Current Limiting
- Programmable Prescaler 1, 6 - 11
- Post Scaler Frequency Divide by 1 or 2
- Drivers with 15mA/24V Capability
- Outputs 4 Separate Square Waves
- Internal Regulator and Bias Source
- 0kHz to 6kHz Input Signal Range
- $-40^\circ C$ to $+125^\circ C$ Operating Temperature Range



Applications


- Prescaler
- Buffer/Limiter
- Signal Interface
- Automotive Speedometer
- Automotive Speed Control
- Automotive Tachometer

Ordering Information

PART NUMBER	TEMPERATURE RANGE	PACKAGE
HIP9020AP	$-40^\circ C$ to $+125^\circ C$	14 Lead Plastic DIP
HIP9020AB	$-40^\circ C$ to $+125^\circ C$	20 Lead Plastic SOIC (W)

Pinouts

 HIP9020 (PDIP)
 TOP VIEW

 HIP9020 (SOIC)
 TOP VIEW


Programmable Quad Buffer Functional Block Diagram

PRSS-A	PRSS-B	PRSS-C	VO1, VO2, VO3 (POSS HIGH) DIV-BY	VO4 (POSS HIGH) DIV-BY	VO1, VO2 (POSS LOW) DIV-BY	VO3, VO4 (POSS LOW) DIV-BY
0	0	0	2	1	2	1
0	0	1	12	6	12	6
0	1	0	14	7	14	7
0	1	1	16	8	16	8
1	0	0	18	9	18	9
1	0	1	20	10	20	10
1	1	0	22	11	22	11

Specifications HIP9020

Absolute Maximum Ratings

Supply Voltage to Pin 2, V_{CC} (Shunt Regulator)	+24V _{DC} Max
through 300Ω and a Series Diode (1N4005 or Equiv.) or +5.3V	
Max Direct Voltage Supply Source to V_{CC}	
Output Voltage (Sustained) to V01,V02,V03,V04	+24V
Output Load Current (Sink)	+15mA
Input Voltage (Through $40k\Omega$, See Figure 1)	$\pm 100V$

Thermal Information

Thermal Resistance θ_{JA}	90°C/W
Plastic DIP and SOIC Package
Maximum Package Power Dissipation up to +85°C	720mW
Derate above 85°C	11.1mW/°C
Operating Temperature Range	-40°C to +125°C
Storage Temperature Range	-65°C to +150°C
Maximum Junction Temperature	+150°C
Lead Temperature (Soldering 10s)	+265°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Electrical Specifications $T_A = -40^\circ C$ to $+125^\circ C$, $V_{CC} = 5V \pm 0.3V$, Unless Otherwise Specified

PARAMETERS	SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
Power Supply (V_{CC})					
Supply Current	I_{CC}		-	12	mA
SSI Input (Test Point - T.P.A., See Figure 1)					
Max. Operating Frequency	$f_S(\text{MAX})$	40kΩ Source, 0.01μF Input Shunt	-	6	kHz
Input Signal Range		40kΩ Source, 0.01μF Input Shunt	± 0.25	± 100	V
Input Hysteresis		40kΩ Source, 0.01μF Input Shunt	0.15	0.45	V
Input Bias Current		40kΩ Source, 0.01μF Input Shunt	-0.5	+0.5	μA
Other Inputs (PRSS, POSS, POSI - See Function Block Diagram)					
Input Low Voltage	V_{IL}		-	1.5	V
Input High Voltage	V_{IH}		3.5	-	V
Input Current High	I_{IH}	$V_{CC} = V_{IN} = 4.7V$	-	10	μA
Input Current Low	I_{IL}	$V_{CC} = 5.3; V_{IN} = 0.4V$	-10	-	μA
PRSO Output					
Output Voltage Low	V_{OL}	$V_{CC} = 5V$	-	0.4	V
Output Voltage High	V_{OH}	$V_{CC} = 5V$	4.6	-	V
Driver Outputs (V01, V02, V03, V04)					
Output Clamp Voltage		$I_{CC} = 1mA$	24	45	V
Output Current Limit		I_{SC} Current Pulsed	15	30	mA
Output Leakage		$V_{OUT} = 24V$	-	30	μA
Output Saturation Voltage	V_{SAT}	$I_{OUT} = 15mA$	-	1	V
		$I_{OUT} = 1mA$	-	0.4	V




FIGURE 1. TYPICAL AUTOMOTIVE APPLICATION CIRCUIT




FIGURE 2. TYPICAL OUTPUT DRIVER SATURATED "ON" CHARACTERISTIC