The SPH9855LM4H-1 is a high-performance, low power, bottom port silicon digital microphone with a single bit PDM output. Using Knowles' proven high performance SiSonic<sup>™</sup> MEMS technology, the SPH9855LM4H-1 consists of an acoustic sensor, a low noise input buffer, and a sigma-delta modulator. This microphone is ideally suited for automotive applications, with Knowles providing the industry's first AEC-Q103 qualified digital microphone. Its high, 66 dB(A), SNR and 132.5 dB SPL AOP provides a large, distortion-free dynamic range for high-quality voice pickup. Additionally, it features a wide frequency band for proximity detection and has a wide operating temperature range for automotive applications.



# ABSOLUTE MAXIMUM RATINGS

Table 1: Absolute Maximum Ratings

Parameter	Absolute Maximum Rating	Units
Vdd to Ground	-0.5, +5.0	V
DATA, CLOCK, SELECT to Ground	-0.3, +5.0	V
Input Current	±5	mA
Short Circuit to/from DATA	Indefinite to Ground or Vdd	sec
Storage Temperature	-40 to +100	°C
Operating Temperature	-40 to +100	°C

Stresses exceeding these "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only. Functional operation at these or any other conditions beyond those indicated under "Acoustic & Electrical Specifications" is not implied. Exposure beyond those indicated under "Acoustic & Electrical Specifications" for extended periods may affect device reliability.

# Knowles



## **PRODUCT FEATURES**

- AEC-Q100/103 Qualified
- Low Distortion / High AOP
- High SNR
- Low Current Consumption in Low-Power Mode
- Flat Frequency Response
- High Drive Capability
- RF Shielded
- Bottom Port
- Sensitivity Matching
- Supports Dual Multiplexed Channels
- Multiple Performance Modes (Sleep, Low-Power, Normal)
- Ultra-Stable Performance
- Omnidirectional
- Standard SMD Reflow
- LGA Package

## TYPICAL APPLICATIONS

- Automotive In-Cabin Active Noise
   Cancellation
- Automotive eCall Communications
   Systems
- Industrial Beam Forming Applications
- Proximity Detection





# ACOUSTIC & ELECTRICAL SPECIFICATIONS<sup>1</sup>

## Table 2: General Microphone Specifications

Test Conditions: 23  $\pm$ 2°C, 55 $\pm$ 20% R.H., Vdd=1.8 V, Tedge  $\leq$  3ns, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Тур	Max	Units
Supply Voltage	Vdd		1.65	1.8	3.6	V
Low Frequency Rolloff	LFRO	-3dB relative to 1 kHz	-	25	-	Hz
High Frequency Flatness		+3dB relative to 1 kHz	-	22	-	kHz
Resonant Frequency Peak	Fres	Free Field response	-	36	-	kHz
DC Offset		Fullscale = ±100	-3.25	-	0.1	% FS
Directivity			Omnidirect	onal		
Polarity		Increasing sound pressure	Increasing	density of 1's	6	
Data Format			1/2 Cycle PE	DM		
Sensitivity Drop		Vdd(min) ≤ Vdd ≤ Vdd(max)	-	-	±0.25	dB
Clock Input Capacitance	Cin		-	15	-	pF
Data Output Capacitance	Cout		-	55	-	pF
Data Output Load	Cload		-	-	110	pF
SELECT (high)			Vdd-0.2	-	3.6	V
SELECT (low)			-0.3	-	0.2	V
Short Circuit Current	lsc	Grounded DATA pin	1	-	20	mA
Fall-asleep Time <sup>3,4</sup>		Fclock < 250kHz	-	-	10	ms
Wake-up Time <sup>3,5</sup>		Fclock ≥ 500kHz	-	-	35	ms
Startup Time <sup>3</sup>		Powered Down $\rightarrow$ Active, S within 1 dB of final value	-	-	35	ms
Time to First Data Bit <sup>6</sup>		Time from valid Vdd and CLK until the first logical bit is driven on the DATA line. The output is tristate until First Data Bit.		4		ms
Mode-Change Time <sup>3, 6</sup>		Low Power Mode ⇔ Normal Mode	-	-	17	ms





## Table 3: Normal Mode

Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8 V, Fclock = 2.4 MHz (D.C. = 50%), Tedge ≤ 3ns, SELECT grounded, no load, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Тур	Max	Units
		Fclock = 1.2 MHz	-	650	690	
		Fclock = 1.536 MHz	-	750	820	
Supply Current <sup>2</sup>	ldd	Fclock = 2.4 MHz	800	1000	1200	μA
		Fclock = 3.072 MHz	-	1225	1350	
		Fclock = 4.8 MHz	-	1850	2000	
Sensitivity	S	94 dB SPL @ 1 kHz	-38	-37	-36	dBFS
		94 dB SPL @ 1 kHz, A-weighted, Fclock = 1.2 MHz	-	64.5	-	
	SNR	94 dB SPL @ 1 kHz, A-weighted, Fclock = 1.536 MHz	-	66	-	
Signal to Noise Ratio		94 dB SPL @ 1 kHz, A-weighted, Fclock = 2.4 MHz	-	66	-	dB(A)
		94 dB SPL @ 1 kHz, A-weighted, Fclock = 3.072 MHz	-	66	-	
		94 dB SPL @ 1 kHz, A-weighted, Fclock = 4.8 MHz	-	66	-	
Near-Ultrasonic SNR		94 dB SPL, @ 19 kHz , BW = 18.5 - 20.0 kHz	-	78	-	dB
	THD	94 dB SPL @ 1 kHz	-	0.05	-	%
Total Harmonic Distortion		115 dB SPL @ 1 kHz	-	0.2	-	70
		1% THD @ 1 kHz, S = typ	-	130.5	-	dB SPL
Acoustic Overload Point	AOP	10% THD @ 1 kHz, S = typ	-	132.5	-	dB SPL
Power Supply Rejection Ratio	PSRR	200 mVpp sinewave @ 1 kHz	-	86	-	dB V/FS
Power Supply Rejection	PSR+N	200 mVpp 7/8 duty cycle rectangular waveform @ 217 Hz, A-weighted	-	-98	-	dBFS(A)

## Table 4: Low-Power Mode

Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8 V, Fclock = 768 kHz (D.C. = 50%), Tedge ≤ 3ns, SELECT grounded, no load, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Тур	Max	Units
Supply Current <sup>2</sup>	Idd		240	260	330	μA
Sensitivity	S	94 dB SPL @ 1 kHz	-22	-21	-20	dBFS
Signal to Noise Ratio	SNR	94 dB SPL @ 1 kHz, A-weighted (BW = 8 kHz)	-	64.5	-	dB(A)
Total Harmonic Distortion	THD	94 dB SPL @ 1 kHz	-	0.05	-	%
Total Harmonic Distontion		1% THD @ 1 kHz, S = typ	-	113	-	dB SPL
Acoustic Overload Point	AOP	10% THD @ 1 kHz, S = typ	7	116	-	dB SPL
Power Supply Rejection Ratio	PSRR	200 mVpp sinewave @ 1 kHz	-	75	-	dBV/FS
Power Supply Rejection	PSR+N	200 mVpp 7/8 duty cycle rectangular waveform @ 217 Hz, A-weighted	-	-85	-	dBFS(A)





## Table 5: Sleep Mode

Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8 V, Fclock = 0 Hz, SELECT grounded, no load, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Тур	Max	Units
Sleep Current	Isleep		-	40	55	μA

<sup>1</sup> Sensitivity and Supply Current are 100% tested.

<sup>2</sup> Idd varies with Cload according to:  $\Delta$ Idd = 0.5\*Vdd\* $\Delta$ Cload\*Fclock.

<sup>3</sup> Valid microphones states are: Powered Down Mode (mic off), Sleep Mode (low current, DATA = high-Z, fast startup), Low-Power Mode (low clock speed) and Normal Mode.

<sup>4</sup> Time from Fclock < 250 kHz to Isleep specification is met when transitioning from Active Mode to Sleep Mode.

 $^{5}$  Time from Fclock  $\ge$  500 kHz to all applicable specifications are met when transitioning from Sleep Mode to Active Mode.

<sup>6</sup> Audio is temporarily muted during the transition between any microphone state.

## Table 6: Digital Interface

Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8 V, Tedge ≤ 3ns, unless otherwise indicated

Parameter	Symbol	Conditions	Min	Тур	Max	Units
Logic Input High <sup>7</sup>	Vih		0.65xVdd	-	3.6	V
Logic Input Low <sup>7</sup>	Vil		-0.3	-	0.35xVdd	V
Logic Output High <sup>7</sup>	Voh	I <sub>OUT</sub> = 2 mA	Vdd-0.45	-	Vdd	V
Logic Output Low <sup>7</sup>	Vol	I <sub>out</sub> = 2 mA	0	-	0.45	V
$Low{\rightarrow}High\;Threshold^8$	VI-h		-	-	0.65xVdd	V
High→Low Threshold <sup>8</sup>	Vh-l		0.35xVdd	-	-	V
Hysteresis Width <sup>8</sup>	Vhyst		0.05xVdd	-	0.20xVdd	V
		Sleep Mode	0	-	250	
Clock Frequency <sup>7</sup>	Fclock	Low-Power Mode	500	-	900	kHz
		Normal Mode	1.1	-	4.8	MHz
Clock Duty Cycle	D.C.		40	50	60	%
Delay Time to Data Line Driven <sup>7</sup>	Tdd		18	-	35	ns
Delay Time to Valid Data <sup>7</sup>	Tdv	Max Cload	-	-	100	ns
Delay Time to High Z <sup>7</sup>	Tdz		5	-	16	ns
Hold Time <sup>7</sup>	Thold	Thold, as observed by the input device, will be dependent on Cload	5	-	-	ns

<sup>7</sup> See Figure 1: Timing Diagram.

<sup>8</sup> See Figure 2: Hysteresis Diagram.



## Figure 1: Timing Diagram



## Figure 2: Hysteresis Diagram



#### Figure 3: State Diagram



## Figure 4: Typical Stereo Application Circuit



#### Figure 5: Typical Single-Microphone Application Circuit



#### NOTES:

All Ground pins must be connected to ground.

If necessary to improve RF performance, optional series components (resistors, ferrites, etc.) should be placed closest to the microphone pads.

Bypass capacitors should be placed near each Vdd pin for best performance. Capacitors near the microphone should not contain Class 2 dielectrics due to their piezoelectric effect.

#### Table 7: SELECT Functionality

Microphone	SELECT	Asserts DATA on	Latch DATA on
Mic (High)	Vdd	CLK rising edge	CLK falling edge
Mic (Low)	Ground	CLK falling edge	CLK rising edge





# PERFORMANCE CURVES

Test Conditions: 23 ±2°C, 55±20% R.H., Vdd=1.8 V, Fclock = 2.4 MHz, SELECT grounded, no load, unless otherwise indicated

## Figure 6: Typical Free Field Magnitude and Masks



	20	100	300	900	1000	1250	3000	8000	10000
USL	-1.5	1	1	1	0	1	1	2	2.5
LSL	-5	-1	-1	-1	0	-1	-1	-1	-1

## Figure 7: Typical THD vs SPI



### Figure 8: Typical Phase and Group Delay



#### Figure 9: Typical THD vs Frequency





# Knowles



### Figure 10: Typical Free Field Ultrasonic Response

## Figure 11: Typical Idd vs Vdd



#### Figure 12: Noise Floor Power Spectral Density



#### Figure 13: Typical PSRR



knowles.com | DATASHEET SPH9855LM4H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.





# MECHANICAL SPECIFICATIONS







Item	Dimension	Tolerance
Length (L)	3.5	±0.10
Width (W)	2.65	±0.10
Height (H)	0.98	±0.10
Acoustic Port (AP)	Ø0.325	±0.05
PCB Thickness (T)	0.307	±0.05

Pin #	Pin Name	Туре	Description
1	DATA	Digital O	PDM Output
2	SELECT	Digital I	Lo/Hi (L/R) Select Connect to Vdd or GND
3	GROUND	Power	Ground
4	CLOCK	Digital I	Clock Input
5	Vdd	Power	Power Supply

## **Example Land Pattern**



## Example Solder Stencil Pattern



## NOTES:



Pick Area only extends to 0.25 mm of any edge or hole unless otherwise specified. Dimensions are in millimeters unless otherwise specified. Tolerance is ±0.15mm unless otherwise specified In the acoustic path, the recommended PCB Hole Diameter is 0.6 ≤ D ≤ 1.0mm, the recom

In the acoustic path, the recommended PCB Hole Diameter is  $0.6 \le D \le 1.0$ mm, the recommended Gasket Cavity Diameter is  $D \ge 1.0$ mm and the recommended Case Hole Diameter is  $1.0 \le D \le 1.5$ mm. Further optimizations based on application should be performed.

8



# **PACKAGING & MARKING DETAIL**



Model Number	Suffix	Reel Diameter	Quantity Per Reel
SPH9855LM4H-1	-8	13"	5900

Component	Surface Resistance (ohms)
Reel	10 <sup>5</sup> - 10 <sup>9</sup>
Carrier Tape	10 <sup>5</sup> - 10 <sup>9</sup>
Cover Tape	10 <sup>4</sup> - 10 <sup>10</sup>



## NOTES

Dimensions are in millimeters unless otherwise specified.

Vacuum pickup only in the pick area indicated in Mechanical Specifications. Tape & reel per EIA-481.

Labels applied directly to reel and external package.

Shelf life: Twelve (12) months when devices are stored in the factory-supplied, unopened ESD moisture sensitive bag under the maximum environmental conditions of 30°C, 70% R.H.

knowles.com | DATASHEET SPH9855LM4H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.

2D barcode "ABCDEFGHJKLMNPQRSTUVWXYZ0123456789": Unique Job Identification Number for product traceability

Letter: "o", orientation mark (pin 1)

"M": Knowles Factory KEM3 "C": Knowles Factory KES2 "P": Knowles KEI

Date Code YWW: "Y": Last digit of year "WW": Work week AA = Internal KN Code

F = Factory Location:





# **RECOMMENDED REFLOW PROFILE**



Profile Feature	Pb-Free	
Average Ramp-up rate ( $T_{SMAX}$ to $T_P$ )	3°C/second max.	
Preheat <ul> <li>Temperature Min (T<sub>SMIN</sub>)</li> <li>Temperature Max (T<sub>SMAX</sub>)</li> <li>Time (T<sub>SMIN</sub> to T<sub>SMAX</sub>) (t<sub>S</sub>)</li> </ul>	150°C 200°C 60-180 seconds	
Time maintained above: • Temperature (T <sub>L</sub> ) • Time (t <sub>L</sub> )	217°C 60-150 seconds	
Peak Temperature (T <sub>P</sub> )	260°C	
Time within 5°C of actual Peak Temperature ( $t_P$ )	20-40 seconds	
Ramp-down rate (T <sub>P</sub> to $T_{SMAX}$ )	6°C/second max	
Time 25°C to Peak Temperature	8 minutes max	

## NOTES

Based on IPC/JDEC J-STD-020 Revision C.

All temperatures refer to topside of the package, measured on the package body surface.

The actual reflow profile used should be optimized based on the reflow requirements of all components, board design, solder paste formulation and reflow equipment used. Details of recommended handling and manufacturing processes can be found in AN25 SMT Manufacturing Guidelines for SiSonic<sup>™</sup> Microphones.

## ADDITIONAL NOTES

- (A) MSL (moisture sensitivity level) Class 1.
- (B) Maximum of 3 reflow cycles is recommended.
- (C) In order to minimize device damage:
  - Do not board wash or clean after the reflow process.
  - Do not brush board with or without solvents after the reflow process.
  - Do not directly expose to ultrasonic processing, welding, or cleaning.
  - Do not insert any object in port hole of device at any time.
  - Do not apply over 30 psi of air pressure into the port hole.
  - Do not pull a vacuum over port hole of the microphone.
  - Do not apply a vacuum when repacking into sealed bags at a rate faster than 0.5 atm/sec.
  - Do not directly expose to vapor phase soldering.

knowles.com | DATASHEET SPH9855LM4H-1 Rev A © 2021, Knowles Electronics, LLC, Itasca, IL, USA, All Rights Reserved. SiSonic, Knowles and the logo are trademarks of Knowles Electronics, LLC.





## MATERIALS STATEMENT

Meets the requirements of the European RoHS directive 2011/65/EC as amended.

Meets the requirements of the industry standard IEC 61249-2-21:2003 for halogenated substances and Knowles Green Materials Standards Policy section on Halogen-Free.

Product is Beryllium Free according to limits specified on the Knowles Hazardous Material List (HSL for Products).

Ozone depleting substances are not used in the product or the processes used to make the product, including compounds listed in Annex A, B, and C of the "Montreal Protocol on Substances That Deplete the Ozone Layer.

# **RELIABILITY SPECIFICATIONS**

Test	Description
Temperature Cycling	500 cycles of thermal shock from -55°C to +125°C with 15 minute soaks (JESD22-A104)
High Temperature Storage Life	+150°C environment for 500 hours (JESD22-A103)
High Temperature Operating Life	+85°C environmental while under bias for 1,000 hours (JESD22-A108)
Low Temperature Storage	-40°C environment for 1,000 hours (JESD22-A119)
Low Temperature Bias	-40°C environment while under bias for 1,000 hours (JESD22-A108)
Temperature/Humidity Storage	+85°C/85% R.H. environment unbiased for 1,000 hours (JESD22-A101A-B)
Temperature/Humidity Bias	+85°C/85% R.H. environment while under bias for 1,000 hours (JESD22-A101A-B)
Temperature/Humidity Cycle 1)	5 cycles (1 cycle = 24 hours). Read point after each cycle.
Temperature/Humidity Cycle 2)	Biased portion of the cycle: 65°C/90%RH, 10 hours at temperature/humidity.
Temperature/Humidity Cycle 3)	Unbiased portion of the cycle: 2 hours ramp down to -10°C/uncontrolled RH, 1 hour at temperature. 2 hours ramp up to 25°C/uncontrolled RH, 1 hour at temperature. (JESD22-A108/IEC 60068-2-2)
Early Life Failure Rate	+105°C environment while under bias for 24 hours (AEC Q100-008)
Variable Frequency Vibration	12 minutes in each X, Y, Z axis from 20 to 2,000 Hz with peak acceleration of 20g (JESD22-B103)
ESD-HBM	3 discharges at ±500V, ±1kV, ±1.5kV and ±2kV direct contact to I/O pins (AEC Q100-002)
ESD-CDM	3 discharges at ±500V and ±750V (AEC Q100-011)
Reflow	5x reflow cycles with peak temperature of +260°C (JEDEC 22-A113F)
Mechanical Shock	3 pulses of 10,000g in each of the X, Y, and Z directions (IEC 68-2-27)
Drop Test	Drop device 10X on each of 6 axes (60 drops total) from a height of 1.2m onto a concrete surface (QRP3032)

## NOTES:

Microphones meet all acoustic and electrical specifications before and after reliability testing, except sensitivity which can deviate up to 3dB.

After 3 reflow cycles, the sensitivity of the microphones shall not deviate more than 1 dB from its initial value.

Temperature Storage testing is covered by Temperature Bias testing as Ta = Tj for Knowles Microphones



# SPECIFICATION REVISIONS

Revision	Specification Changes	Date
A	Intial Release (ECR 21-4349)	5/3/21

Information contained herein is subject to change without notice. It may be used by a party at their own discretion and risk. We do not guarantee any results or assume any liability in connection with its use. This publication is not to be taken as a license to operate under any existing patents.

Knowles Corporation 1151 Maplewood Drive Itasca, Illinois 60143 Phone: 1 (630) 250-5100 Fax: 1 (630) 250-0575 sales@knowles.com Model/Reference Number: Datasheet SPH9855LM4H-1 Rev A © Copyright 2021 Knowles

