

ILONA-RS

~10° spot beam

SPECIFICATION:

Dimensions	Ø 49.8 mm
Height	29.3 mm
Fastening	socket
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
ILONA-RS	Single lens	PMMA	clear	



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C16686_ILONA-RS » Box size: 480 x 280 x 300 mm	264	99	33	9.6




See also our general installation guide: www.ledil.com/installation_guide


OPTICAL RESULTS (MEASURED):




LED V11 HD Gen 8
FWHM / FWTM 20.0° / 40.0°
Efficiency 93 %
Peak intensity 5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 633d Hekla




LED V6 HD Gen 7
FWHM / FWTM 13.0° / 24.0°
Efficiency 94 %
Peak intensity 13.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 634c Hekla



LED V6 HD Gen 7
FWHM / FWTM 14.0° / 23.0°
Efficiency 95 %
Peak intensity 13.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C




LED Vesta DTW 9mm (4W/6W/12W)
FWHM / FWTM 19.0° / 34.0°
Efficiency 93 %
Peak intensity 6.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 490 Typ L8



OPTICAL RESULTS (MEASURED):




LED Vesta TW 6mm DP
FWHM / FWTM 14.0° / 25.0°
Efficiency 91 %
Peak intensity 12.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 504 Typ L8





CITIZEN

LED CLU700/701/702/703
FWHM / FWTM 12.0° / 22.0°
Efficiency 96 %
Peak intensity 15.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C





CITIZEN

LED CLU7A2/7A3
FWHM / FWTM 9.0° / 17.0°
Efficiency 94 %
Peak intensity 26 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C



CITIZEN



LED CLU7B2
FWHM / FWTM 8.0° / 16.0°
Efficiency 94 %
Peak intensity 32.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C



OPTICAL RESULTS (MEASURED):


LUMILEDS

LED LUXEON CX Plus CoB L08 (Gen2)
FWHM / FWTM 28.0° / 52.0°
Efficiency 93 %
Peak intensity 3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 637a Hekla




LUMILEDS

LED LUXEON CX Plus CoB - HD S01H4
FWHM / FWTM 12.0° / 22.0°
Efficiency 94 %
Peak intensity 16 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 634c Hekla




LUMILEDS

LED LUXEON CX Plus CoB - HD S02H6
FWHM / FWTM 13.0° / 24.0°
Efficiency 94 %
Peak intensity 13.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 634c Hekla



LUMILEDS


LED LUXEON CX Plus CoB - HD S04H9
FWHM / FWTM 19.0° / 33.0°
Efficiency 94 %
Peak intensity 7 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 634c Hekla




OPTICAL RESULTS (MEASURED):





LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 FWHM / FWTM 23.0° / 41.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 637a Hekla




LED LUXEON CX Plus CoB M02 / M03 (Gen2)
 FWHM / FWTM 17.0° / 32.0°
 Efficiency 93 %
 Peak intensity 7.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 641a Hekla



LED LUXEON CX Plus CoB S01 (Gen2)
 FWHM / FWTM 12.0° / 23.0°
 Efficiency 93 %
 Peak intensity 14.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 634c Hekla




LED CXM-3
 FWHM / FWTM 9.0° / 16.0°
 Efficiency 94 %
 Peak intensity 31.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 F15255_HEKLA-SOCKET-C





OPTICAL RESULTS (MEASURED):





LED CXM-4
FWHM / FWTM 10.0° / 19.0°
Efficiency 94 %
Peak intensity 21.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C



LED OSTAR Stage (S2WN)
FWHM / FWTM 7.0° / 13.0°
Efficiency 94 %
Peak intensity 42.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I





LED OSTAR Stage (S2WP)
FWHM / FWTM 9.0° / 16.0°
Efficiency 94 %
Peak intensity 29.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I











SEOUL SEMICONDUCTOR

LED MJT COB LES 14.5
FWHM / FWTM 31.0° / 55.0°
Efficiency 94 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17438_HEKLA-G2-I





OPTICAL RESULTS (MEASURED):

<p>SEOUL SEMICONDUCTOR</p> <p>LED MJT COB LES 6</p> <p>FWHM / FWTM 12.0° / 22.0°</p> <p>Efficiency 95 %</p> <p>Peak intensity 15.8 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components: F17435_HEKLA-G2-C</p>		
<p>SEOUL SEMICONDUCTOR</p> <p>LED MJT COB LES 9.8</p> <p>FWHM / FWTM 20.0° / 34.0°</p> <p>Efficiency 95 %</p> <p>Peak intensity 6.4 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components: F17435_HEKLA-G2-C</p>		
<p>TRIDONIC</p> <p>LED SLE G7 LES09</p> <p>FWHM / FWTM 20.0° / 32.0°</p> <p>Efficiency 95 %</p> <p>Peak intensity 7.2 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components: F15255_HEKLA-SOCKET-C</p>		
<p>XICATO</p> <p>LED XOB 6 mm</p> <p>FWHM / FWTM 14.0° / 23.0°</p> <p>Efficiency 93 %</p> <p>Peak intensity 13.5 cd/lm</p> <p>LEDs/each optic 1</p> <p>Light colour White</p> <p>Required components: F15255_HEKLA-SOCKET-C</p>		

OPTICAL RESULTS (MEASURED):

XICATO


LED XOB 9.8 mm
FWHM / FWTM 19.0° / 32.0°
Efficiency 94 %
Peak intensity 7.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C




OPTICAL RESULTS (SIMULATED):




LED V13 Gen 8
FWHM / FWTM 30.0° / 50.0°
Efficiency 93 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I




LED V4 HD Gen 7
FWHM / FWTM 10.0° / 20.0°
Efficiency 95 %
Peak intensity 24.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15253_HEKLA-SOCKET-A



LED V9 HD Gen7
FWHM / FWTM 18.0° / 30.0°
Efficiency 94 %
Peak intensity 8.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I




LED Vero SE 10
FWHM / FWTM 16.0° / 34.0°
Efficiency 94 %
Peak intensity 7.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (SIMULATED):


CITIZEN

LED CLL02x/CLU02x (LES10)
FWHM / FWTM 18.0° / 33.0°
Efficiency 92 %
Peak intensity 7.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C




CITIZEN

LED CLU710/711
FWHM / FWTM 17.0° / 30.0°
Efficiency 92 %
Peak intensity 9.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15859_HEKLA-SOCKET-I




CITIZEN

LED CLU712/713
FWHM / FWTM 18.0° / 31.0°
Efficiency 94 %
Peak intensity 8.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17438_HEKLA-G2-I




LED CHA0304
FWHM / FWTM 9.0° / 18.0°
Efficiency 95 %
Peak intensity 27.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17435_HEKLA-G2-C




OPTICAL RESULTS (SIMULATED):




LED CHA0410
FWHM / FWTM 10.0° / 20.0°
Efficiency 95 %
Peak intensity 21.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17435_HEKLA-G2-C




LED CMA1303
FWHM / FWTM 10.0° / 20.0°
Efficiency 95 %
Peak intensity 22.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17439_HEKLA-G2-J



LED CMA1306
FWHM / FWTM 12.0° / 24.0°
Efficiency 95 %
Peak intensity 15.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15956_HEKLA-SOCKET-J




LED CXA/B 13xx
FWHM / FWTM 13.0° / 24.0°
Efficiency 93 %
Peak intensity 15 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15956_HEKLA-SOCKET-J




OPTICAL RESULTS (SIMULATED):




LED CXA/B 15xx
FWHM / FWTM 20.0° / 32.0°
Efficiency 92 %
Peak intensity 7.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17436_HEKLA-G2-D




LED CXA/B 15xx
FWHM / FWTM 19.0° / 32.0°
Efficiency 93 %
Peak intensity 7.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15256_HEKLA-SOCKET-D



LED CXA/B 1816 & CXA/B 1820 & CXA 1850
FWHM / FWTM 23.0° / 40.0°
Efficiency 93 %
Peak intensity 4.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15254_HEKLA-SOCKET-B




LED LUXEON CoB 1202/1203
FWHM / FWTM 18.0° / 33.0°
Efficiency 93 %
Peak intensity 7.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17437_HEKLA-G2-H



OPTICAL RESULTS (SIMULATED):


LUMILEDS

LED LUXEON CoB 1202s
FWHM / FWTM 12.0° / 24.0°
Efficiency 95 %
Peak intensity 15.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15858_HEKLA-SOCKET-H




LUMILEDS

LED LUXEON CoB 1204/1205
FWHM / FWTM 26.0° / 44.0°
Efficiency 94 %
Peak intensity 3.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LUMILEDS

LED LUXEON CoB 1204HD
FWHM / FWTM 20.0° / 32.0°
Efficiency 94 %
Peak intensity 7.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17437_HEKLA-G2-H



LUMILEDS


LED LUXEON CoB 1205HD
FWHM / FWTM 24.0° / 39.0°
Efficiency 94 %
Peak intensity 5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17437_HEKLA-G2-H




OPTICAL RESULTS (SIMULATED):




LED LUXEON CoB 1208
FWHM / FWTM 27.0° / 50.0°
Efficiency 91 %
Peak intensity 3.2 cd/Im
LEDs/each optic 1
Light colour White
Required components:
C16142_HEKLA-SOCKET-K




LED CxM-6 (13.5x13.5)
FWHM / FWTM 14.0° / 25.0°
Efficiency 94 %
Peak intensity 13.4 cd/Im
LEDs/each optic 1
Light colour White
Required components:
F15255_HEKLA-SOCKET-C



LED COB S-Type (LES 6)
FWHM / FWTM 12.0° / 24.0°
Efficiency 93 %
Peak intensity 15.4 cd/Im
LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G




LED COB S-Type (LES 6)
FWHM / FWTM 12.0° / 24.0°
Efficiency 93 %
Peak intensity 15.6 cd/Im
LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G




OPTICAL RESULTS (SIMULATED):




LED COB S-Type (LES 7)
FWHM / FWTM 16.0° / 26.0°
Efficiency 95 %
Peak intensity 11.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G




LED NFSWE11A
FWHM / FWTM 18.0° / 30.0°
Efficiency 88 %
Peak intensity 8.4 cd/lm
LEDs/each optic 30
Light colour White
Required components:
C16142_HEKLA-SOCKET-K



LED Fortimo SLM L13 CoB
FWHM / FWTM 24.0° / 44.0°
Efficiency 93 %
Peak intensity 4.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 632a Hekla XL




LED Fortimo SLM L15 CoB
FWHM / FWTM 28.0° / 52.0°
Efficiency 92 %
Peak intensity 3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 632a Hekla XL



OPTICAL RESULTS (SIMULATED):


PHILIPS

LED Fortimo SLM L15 CoB
FWHM / FWTM 26.0° / 50.0°
Efficiency 93 %
Peak intensity 3.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 632a Hekla XL




SAMSUNG

LED LC010C
FWHM / FWTM 14.0° / 24.0°
Efficiency 94 %
Peak intensity 14.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F15848_HEKLA-SOCKET-G




SAMSUNG

LED LC020C
FWHM / FWTM 14.0° / 24.0°
Efficiency 94 %
Peak intensity 13.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17438_HEKLA-G2-I



XICATO

LED XTM - 9mm LES
FWHM / FWTM 18.0° / 32.0°
Efficiency 94 %
Peak intensity 8.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C15743_XTM-ADAPTER-50-B



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)