

## General Description

The AOZ1334ADI-02 is a single channel load switch with very low on-resistance in a small package. It contains an n-channel MOSFET for up to 5.5V input voltage operation and 10A current channel with 5V bias supply. The load switch is controlled by a low voltage control signal through ON pin.

The AOZ1334ADI-02 integrates an internal 220Ω load resistor for quick output discharge when load switch is off.

The AOZ1334ADI-02 is available in a 3mm x 3mm DFN-8L package with bottom thermal pad and is rated over a -40°C to +85°C ambient temperature range.

## Features


- 0.8V to 5.5V input voltage range
- 10A continuous current
- Low  $R_{DS(ON)}$  internal NFETs  
– 3.6mΩ at  $V_{BIAS} = 5V$ ,  $V_{IN} = 1.05V$
- 60μA low quiescent current
- 0.5ms turn on rise time at  $V_{BIAS} = 5V$  and  $V_{IN} = 1.05V$
- 2.5V to 5.5V bias voltage
- Integrated quick output discharge resistor
- Thermally enhanced 3mm x 3mm DFN-8L package

## Applications

- Portable computers
- Ultrabooks
- Tablet PCs
- Set top boxes
- LCD TVs
- Telecom/Networking/Datacom equipment
- SSD
- Consumer electronics



## Typical Application



## Ordering Information


Part Number	Temperature Range	Package	Environmental
AOZ1334ADI-02	-40°C to +85°C	3mm x 3mm DFN-8L	Green




All AOS products are offered in packages with Pb-free plating and compliant to RoHS standards.

Please visit [www.aosmd.com/media/AOSGreenPolicy.pdf](http://www.aosmd.com/media/AOSGreenPolicy.pdf) for additional information.

## Pin Configuration



3mm x 3mm DFN-8  
(Top View)



3mm x 3mm DFN-8  
(Bottom View)

## Pin Description

Pin Number	Pin Name	Pin Function
1, 2, EPAD	IN	Load Switch Input. Bypass capacitor is recommended to minimize input voltage dip. Recommended voltage range of this pin is 0.8V to 5.5V to obtain optimal $R_{ON}$ .
3	VBIAS	Bias Voltage. Power supply input for the device. Recommended voltage range is 2.5V to 5.5V.
4	ON	Active High Switch Control Input. Do not leave floating.
5	GND	Ground.
6, 7, 8	OUT	Load switch output.

## Absolute Maximum Ratings

Exceeding the Absolute Maximum ratings may damage the device.

Parameter	Rating
IN, ON, VBIAS, OUT to GND	-0.3V to 6V
Junction Temperature ( $T_J$ )	+150°C
Storage Temperature ( $T_S$ )	-65°C to +150°C
ESD Rating HBM/CDM	2kV/1kV

## Recommend Operating Ratings

The device is not guaranteed to operate beyond the Maximum Operating Ratings.


Parameter	Rating
Supply Voltage ( $V_{IN}$ )	5.5V
Ambient Temperature ( $T_A$ )	-40°C to +85°C
Package Thermal Resistance	
3x3 DFN-8 ( $\theta_{JC}$ )	8°C/W
3x3 DFN-8 ( $\theta_{JA}$ )	60°C/W

## Electrical Characteristics


$T_A = 25^\circ\text{C}$ ,  $V_{BIAS} = 5\text{V}$ ,  $V_{IN} = 1.05\text{V}$ , unless otherwise specified. Specifications in **BOLD** indicate a temperature range of -40°C to +85°C.

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Units
$V_{IN}$	IN Supply Voltage	$V_{ON} = 5\text{V}$	0.8	1.05	5.5	V
$V_{BIAS}$	VBIAS Supply Voltage		2.5	5	5.5	V
$I_D$	Maximum Continuous Current	$V_{ON} = 5\text{V}$		10		A
$I_{PLS}$	Maximum Pulsed Switch Current	$V_{IN} = V_{ON} = 5\text{V}$ Pulse < 300 $\mu\text{s}$ , 2% Duty Cycle		12		A
$I_q$	Quiescent Supply Current of $V_{BIAS}$	$I_{OUT} = 0\text{V}$ , $V_{ON} = 5\text{V}$		60		$\mu\text{A}$
$I_{OFF}$	VBIAS Shutdown Supply Current	$V_{ON} = 0\text{V}$ , $V_{OUT} = 0\text{V}$			2	$\mu\text{A}$
$I_{INOFF}$	IN Shutdown Supply Current	$V_{ON} = 0\text{V}$ , $V_{OUT} = 0\text{V}$			2	$\mu\text{A}$
$I_{ON}$	ON Leakage Current	$V_{ON} = 5\text{V}$			1	$\mu\text{A}$
$V_{ONH}$	ON High Level Voltage		1.2			V
$V_{ONL}$	ON Low Level Voltage				0.5	V
<b>Switching ON Resistance</b>						
$R_{ON}$	Switch ON-State Resistance	$I_{OUT} = -6\text{A}$ , $V_{ON} = 5\text{V}$ , $V_{BIAS} = 5\text{V}$		4.5	5	m $\Omega$
		$I_{OUT} = -6\text{A}$ , $V_{ON} = 5\text{V}$ , $V_{BIAS} = 3.3\text{V}$		4.5	5	m $\Omega$
$R_{PD}$	Output Pull-Down Resistance	$I_{OUT} = 15\text{mA}$ , $V_{ON} = 0\text{V}$		220	300	$\Omega$

## Functional Block Diagram







## Switching Characteristics









Test conditions:  $T_A = 25^\circ\text{C}$ ,  $C_{IN} = 1\mu\text{F}$ ,  $C_L = 0.1\mu\text{F}$  (unless otherwise specified).

Symbol	Parameter	Min.	Typ.	Max.	Units
<b><math>V_{IN} = 1.05\text{V}</math>, <math>V_{BIAS} = V_{ON} = 5\text{V}</math>, <math>R_L = 10\Omega</math></b>					
$t_{ON}$	Turn-ON Time		800		$\mu\text{s}$
$t_{D-ON}$	Turn-ON Delay time	300	500	650	
$t_R$	Turn-ON Rise Time	300	500	650	
$t_{OFF}$	Turn-OFF Time		2.8		
$t_F$	Turn-OFF Fall Time		2.0		
<b><math>V_{IN} = 1.5\text{V}</math>, <math>V_{BIAS} = V_{ON} = 5\text{V}</math>, <math>R_L = 10\Omega</math></b>					
$t_{ON}$	Turn-ON Time		830		$\mu\text{s}$
$t_{D-ON}$	Turn-ON Delay time	280	480	624	
$t_R$	Turn-ON Rise Time	380	600	780	
$t_{OFF}$	Turn-OFF Time		2.5		
$t_F$	Turn-OFF Fall Time		2.0		
<b><math>V_{IN} = 1.05\text{V}</math>, <math>V_{BIAS} = V_{ON} = 5\text{V}</math>, <math>I_{OUT} = -6\text{A}</math></b>					
$t_{ON}$	Turn-ON Time		1140		$\mu\text{s}$
$t_{D-ON}$	Turn-ON Delay time		660		
$t_R$	Turn-ON Rise Time		700		
$t_{OFF}$	Turn-OFF Time		2.3		
$t_F$	Turn-OFF Fall Time		0.5		
<b><math>V_{IN} = 1.5\text{V}</math>, <math>V_{BIAS} = V_{ON} = 5\text{V}</math>, <math>I_{OUT} = -6\text{A}</math></b>					
$t_{ON}$	Turn-ON Time		1120		$\mu\text{s}$
$t_{D-ON}$	Turn-ON Delay time		630		
$t_R$	Turn-ON Rise Time		770		
$t_{OFF}$	Turn-OFF Time		2.0		
$t_F$	Turn-OFF Fall Time		0.5		





## Typical Characteristics



Typical Characteristics (Continued)




Typical Characteristics (Continued)




## Functional Characteristics


**Turn-ON & Turn-ON Rise Times**  
( $V_{INX}=1.05V$ ,  $V_{BIAS}=5V$ ,  $C_{IN}=1\mu F$ ,  $C_L=0.1\mu F$ ,  $R_L=10\Omega$ )




**Turn-ON & Turn-ON Rise Times**  
( $V_{INX}=1.5V$ ,  $V_{BIAS}=5V$ ,  $C_{IN}=1\mu F$ ,  $C_L=0.1\mu F$ ,  $R_L=10\Omega$ )




**Turn-OFF & Turn-OFF Fall Times**  
( $V_{INX}=1.05V$ ,  $V_{BIAS}=5V$ ,  $C_{IN}=1\mu F$ ,  $C_L=0.1\mu F$ ,  $R_L=10\Omega$ )




**Turn-OFF & Turn-OFF Fall Times**  
( $V_{INX}=1.5V$ ,  $V_{BIAS}=5V$ ,  $C_{IN}=1\mu F$ ,  $C_L=0.1\mu F$ ,  $R_L=10\Omega$ )



**Turn-ON & Turn-OFF at  $I_{OUT}=-6A$**   
( $V_{INX}=1.05V$ ,  $V_{BIAS}=5V$ ,  $C_{IN}=1\mu F$ ,  $C_L=0.1\mu F$ )



**Turn-ON & Turn-OFF at  $I_{OUT}=-6A$**   
( $V_{INX}=1.5V$ ,  $V_{BIAS}=5V$ ,  $C_{IN}=1\mu F$ ,  $C_L=0.1\mu F$ )





## Detailed Description

### ON/OFF Control

The AOZ1334ADI-02 is enabled when the ON pin is on active high with 1.2V or above voltage. The device is disabled when the ON pin voltage is 0.5V or lower. The EN input is compatible with both TTL and CMOS logic.

### VBIAS Voltage Range

For optimal on-resistance of load switch, make sure the voltage is within 2.5V to 5.5V. On-resistance of load switch will be higher if the condition is not satisfied. Resistance curves of a typical sample device at  $V_{BIAS} = V_{IN}$  and at different output currents are shown as below.



## Applications Information

The basic AOZ1334ADI-02 application circuit is shown in the first page. Component selection is explained below.

### Input Capacitor

A capacitor of 10μF or higher value is recommended to be placed close to the IN pins of AOZ1334ADI-02. This capacitor can reduce the voltage drop caused by the in-rush current during the turn-on transient of the load switch. A higher value capacitor can be used to further reduce the voltage drop during high-current application.

### Output Capacitor

A capacitor of 10μF or higher value is recommended to be placed between the OUT pins and GND. The capacitance does not affect the turn-on slew rate. However, a larger capacitor makes the initial turn-on transient smoother.

### Thermal Considerations

To ensure proper operation, the maximum junction temperature of the AOZ1334ADI-02 should not exceed 150°C. Several factors attribute to the junction temperature rise: load current, MOSFET on-resistance, junction-to-ambient thermal resistance, and ambient temperature. The maximum load current can be determined by:

$$I_{LOAD(MAX)} = \sqrt{\frac{T_{J(MAX)} - T_C}{\Theta_{JC} \times R_{DS(ON)}}$$

It is noted that the maximum continuous load current is 10A. Exceeding the maximum continuous load current may cause permanent damage to the device.


## Layout Guidelines

Good PCB is important for improving the thermal performance of AOZ1334ADI-02. Place the input and output bypass capacitors close to the IN and OUT pins. The input and output PCB traces should be as wide as possible for the given PCB space. Use a ground plane to enhance the power dissipation capability of the device.



### Tape and Reel Dimensions, DFN3x3-8L


#### Carrier Tape



UNIT: mm

Package	A0	B0	K0	D0	D1	E	E1	E2	P0	P1	P2	T
DFN 3x3_EP	3.40 ±0.10	3.35 ±0.10	1.10 ±0.10	1.50 +0.10/-0.0	1.50 +0.10/-0.0	12.00 ±0.30	1.75 ±0.10	5.50 ±0.05	8.00 ±0.10	4.00 ±0.10	2.00 ±0.05	0.30 ±0.05

#### Reel




UNIT: mm


Tape Size	Reel Size	M	N	W	W1	H	K	S	G	R	V
12mm	ø330	ø330.00 ±0.50	ø97.00 ±0.10	13.00 ±0.30	17.40 ±1.00	ø13.00 +0.5/-0.2	10.60	2.00 ±0.50	N/A	N/A	N/A

#### Leader / Trailer & Orientation

Unit Per Reel:  
5000pcs



## Package Marking



### LEGAL DISCLAIMER

Applications or uses as critical components in life support devices or systems are not authorized. AOS does not assume any liability arising out of such applications or uses of its products. AOS reserves the right to make changes to product specifications without notice. It is the responsibility of the customer to evaluate suitability of the product for their intended application. Customer shall comply with applicable legal requirements, including all applicable export control rules, regulations and limitations.

AOS's products are provided subject to AOS's terms and conditions of sale which are set forth at:  
[http://www.aosmd.com/terms\\_and\\_conditions\\_of\\_sale](http://www.aosmd.com/terms_and_conditions_of_sale)

### LIFE SUPPORT POLICY

ALPHA AND OMEGA SEMICONDUCTOR PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.