



■ Features

- Ideal for printed circuit board mounting
- The plastic material used carries Underwriters Laboratory flammability recognition 94V-0
- Built-in printed circuit board stand-offs
- High case dielectric strength
- High temperature soldering guaranteed 260°C/5 seconds at 5 lbs (2.3kg) tension

■ Mechanical Data

- Case: Reliable low cost construction utilizing molded plastic technique
- Terminals: Plated leads solderable per MIL-STD-202, Method 208
- Mounting Position: Any

■ Maximum Ratings & Thermal Characteristics


Parameter	Symbol	2W005	2W01	2W02	2W04	2W06	2W08	2W10	Unit
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS bridge input voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified output current at TC=40°C	I _{F(AV)}				2				A
Peak forward surge current single sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}				30				A
Operating junction and storage temperature range	T _J T _{STG}				-55 to + 150				°C

Notes: Rating at 25°C ambient temperature unless otherwise specified, Resistive or Inductive load, 60 Hz. For Capacitive load derate current by 20%.

■ Electrical Characteristics

Parameter	Symbol	2W005	2W01	2W02	2W04	2W06	2W08	2W10	Unit
Maximum instantaneous forward voltage drop per leg at 2A	V _F				1.1				V
Maximum DC reverse current at rated DC blocking voltage per element TA=25°C TA=125°C	I _R				10				uA

Notes: Rating at 25°C ambient temperature unless otherwise specified, Resistive or Inductive load, 60 Hz. For Capacitive load derate current by 20%. Thermal resistance from Junction to Ambient on P.C.board mounting. Measured at 2.0 MHz and applied reverse voltage of 4.0 volts



Dimensions in inches and (millimeters)



■ Rating and Characteristic Curves (TA=25°C Unless otherwise noted)

Fig. 1 Derating Curve for Output Rectified Current




Fig. 3 Typical Instantaneous Forward Characteristics




Fig. 2 Maximum Non-repetitive Peak Forward Surge Current




Fig. 4 Typical Reverse Characteristics




Fig. 5 Typical Junction Capacitance

