

HDP26-24-21SE-L015

✓ ACTIVE

DEUTSCH | DEUTSCH HD, DEUTSCH HDP

TE Internal #: HDP26-24-21SE-L015

Housing for Female Terminals, Wire-to-Wire, 21 Position, Sealable, Black, Wire & Cable, Power & Signal, Cable Mount (Free-Hanging), Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Connector System: **Wire-to-Wire**
Number of Positions: **21**
Connector & Housing Type: **Housing for Female Terminals**
Sealable: **Yes**
Mating Pin Diameter: **1.59 mm, 2.39 mm [.063 in, .094 in]**

[All DEUTSCH HDP20 Housings \(324\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Contact Retainer

Configuration Features

Blank Cavity Position	0
Connector Modification	Threaded Adapter
Connector Seal Code	E Seal
Number of Positions	21



Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 48 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 12, Size 16
Contact Type	Socket
Mating Pin Diameter	1.59 mm, 2.39 mm[.063 in][.094 in]
Contact Current Rating (Max)	13 A, 25 A

Mechanical Attachment

Terminal Position Assurance	No
Strain Relief	Add By Accessory
Mating Alignment Type	Guide Slot
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA GF
------------------	-------

Dimensions

Connector Height	49.53 mm[1.95 in]
Product Width	49.53 mm[1.95 in]
Product Length	55.45 mm[2.183 in]
Compatible Insulation Diameter Range	1.35 – 3.05 mm, 2.46 – 4.01 mm[.053 – .12 in][.097 – .158 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP67
----------------------	------



UL Flammability Rating

20mm Flame Test per Standard UL-94

Packaging Features

Packaging Quantity	1
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # CAT-D48-SP729 DEUTSCH Sealing Plugs	 TE Part # CAT-H396-B128 DEUTSCH HDP20 Backshells	 TE Part # CAT-H3910-B128 DEUTSCH HD10 Backshells	 TE Part # CAT-J67-DSCC16 DEUTSCH Size 16 Crimp Contacts
 TE Part # CAT-D48-ST273 DEUTSCH Solid Contacts	 TE Part # HD30-24BT-BK BOOT, 24SZ, ST, BLK	 TE Part # 1062-12-0144 SOC, SF, SIZE 12, 12-14, AU/SN	 TE Part # HD30-24BT BOOT, 24SZ, ST, GRY
 TE Part # HD30-24BT-90-BK BOOT, 24SZ, RA, BLK	 TE Part # SRN21 SEAL RING, CONDUIT ADAPTER, NW22	 TE Part # CN21 CAP NUT, CONDUIT ADAPTER, NW22	 TE Part # 0411-337-1205 EXT TOOL, SIZE 12, 12-14 AWG, E, ORG
 TE Part # HDP24-24-21PE-L015 REC, 21P, BLK, E, THD, 12/16, P	 TE Part # WHDS-24-1 STRAIN RELIEF, HD30, 24SZ, ST	 TE Part # WHDS-24-2 STRAIN RELIEF, HD30, 24SZ, RA	 TE Part # 1062-12-0222 SOC, SF, SIZE 12, 10, NI/NI
 TE Part # 1062-12-0166 SOC, SF, SIZE 12, 12-14, NI/SN	 TE Part # 0411-336-1605 EXT TOOL, SIZE 16, 16-20 AWG, E, DRK BLU		

Also in the Series | **DEUTSCH HD**



Automotive Connector Caps & Covers
(32)



Automotive Housings(742)



Connector Backshells(29)



Connector Seals & Cavity Plugs(10)




Connector Strain Relief(5)



Insertion & Extraction Tools(11)



Other Automotive Connector
Accessories(11)



PCB Headers & Receptacles(1)

Also in the Series

DEUTSCH HDP



Automotive Connector Caps & Covers
(4)



Automotive Housings(331)



Connector Backshells(8)



Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(11)



Other Automotive Connector
Accessories(5)

Customers Also Bought



Documents

Product Drawings

PLG, 21P, BLK, E, THD, 12/16, S

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP26-24-21SE-L015_99_c-hdp26-24-21se-l015-99.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-24-21SE-L015_99_c-hdp26-24-21se-l015-99.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-24-21SE-L015_99_c-hdp26-24-21se-l015-99.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English