

Passive Components &gt; Resistors &gt; Surface Mount Resistors

Resistor Type: **Power Resistor**Number of Terminations: **2**Package Size Code: **1225**Packaging Method: **Taped & Reeled**Passive Component Tolerance: **1 %**

## Features

### Product Type Features

Resistor Type	Power Resistor
Package Size Code	1225
Element Type	Thick Film

### Configuration Features

Number of Resistors	1
---------------------	---

### Electrical Characteristics

Operating Voltage	200 V
Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	24 Ω
Power Rating	3 W

### Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

## Dimensions

Product Height	.65 mm [.025 in]
Product Length	3.2 mm [.126 in]
Product Width	6.4 mm [.252 in]

## Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±200 ppm/°C

## Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com/compliance)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

TE Part # 3-2176564-5  
3430 A3 1% 24R 200ppm 4k RL

## Also in the Series | CGS 3430



Surface Mount Resistors(1168)

## Customers Also Bought

TE Part #4-2176566-1  
3430 A3 1% 43R 100ppm 1k RLTE Part #4-2176566-3  
3430 A3 1% 51R 100ppm 1k RLTE Part #4-2176566-4  
3430 A3 1% 56R 100ppm 1k RL

## Documents

### Product Drawings

[3430 A3 1% 24R 200ppm 1k RL](#)

English

### CAD Files

[Customer View Model](#)[ENG\\_CVM\\_CVM\\_3-2176566-5\\_BA.3d\\_igs.zip](#)

English

[Customer View Model](#)[ENG\\_CVM\\_CVM\\_3-2176566-5\\_BA.3d\\_stp.zip](#)

English

[Customer View Model](#)[ENG\\_CVM\\_CVM\\_3-2176566-5\\_BA.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[Datasheet - CGS 3430 Series](#)

English

[Automotive Grade Wide Terminal Chip Resistor - Type 3430 Series](#)

English