

CRGCQ1210J22R

✓ ACTIVE

Neohm | Neohm CRGCQ


TE Internal #: 2176346-9

22 Ω , Thick Film, General Purpose Resistor, 5 %, 2 Termination,
1210, Taped & Reeled, .5 W, ± 200 ppm/ $^{\circ}\text{C}$, Solder, Height .022 in [
55 mm], Neohm CRGCQ

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **General Purpose Resistor**
Number of Terminations: **2**
Package Size Code: **1210**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **5 %**

Features

Product Type Features

Resistor Type	General Purpose Resistor
Package Size Code	1210
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Passive Component Tolerance	5 %
Resistance Class	Up to 1k Ω
Resistance Value	22 Ω
Power Rating	.5 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.1 mm[.122 in]
Product Width	2.6 mm[.102 in]

Usage Conditions

Temperature Coefficient	± 200 ppm/ $^{\circ}\text{C}$
-------------------------	-----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CRCGQ1210J22R

22 Ω , Thick Film, General Purpose Resistor, 5 %, 2 Termination, 1210, Taped & Reeled, .5 W, ± 200 ppm/ $^{\circ}\text{C}$, Solder, Height .022 in [.55 mm], Neohm CRCGQ



TE Part # 1-2176341-7
CRCGQ 0805 220R 1%

TE Part # 1-2176345-2
CRCGQ 1210 82R 1%

TE Part # 1-2176347-7
CRCGQ 2010 220R 1%

TE Part # 2176349-4
CRCGQ 2512 18R 1%

TE Part # 1-2176350-2
CRCGQ 2512 68R 5%

Also in the Series | [Neohm CRCGQ](#)

Surface Mount Resistors(728)

Customers Also Bought

TE Part #5227676-1
BNC PCB RT ANGLE JACK

TE Part #5-520315-6
TRIOMATE ASSY V 6P L=3.556LDFR

TE Part #8-640929-1
RECEPT,PIDG FASTON 16-14 110

TE Part #2176345-8
CRCGQ 1210 39R 1%

TE Part #2176347-8
CRCGQ 2010 39R 1%

TE Part #2176348-9
CRCGQ 2010 22R 5%

TE Part #1-2176328-2
CRGP 1206 82R 1%

TE Part #1-640456-9
19P MTA100 HDR ASSY F/L SQ STR



Documents

Product Drawings

[CRGCQ 1210 22R 5%](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2176346-9_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176346-9_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176346-9_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.