



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0805**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0805
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	100 V
Passive Component Tolerance	.1 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	23.7K Ω
Power Rating	.2 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]

Usage Conditions

Temperature Coefficient	± 10 ppm/ $^{\circ}\text{C}$
-------------------------	----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2176372-6
[RQ 0603 56K2 0.1% 10PPM 5K RL](#)

TE Part # 2176371-8
[RQ 0603 5K49 0.1% 10PPM 5K RL](#)

TE Part # 3-2176382-0
[RQ 0805 267K 0.1% 10PPM 5K RL](#)

TE Part # 3-2176389-4
[RQ 1206 237R 0.1% 10PPM 5K RL](#)

TE Part # 4-2176391-2
[RQ 1206 33K2 0.1% 10PPM 5K RL](#)

TE Part # 2-2176376-8
[RQ 0805 23K7 0.1% 10PPM 1K RL](#)

Also in the Series | [Holsworthy RQ73](#)

[Surface Mount Resistors\(3078\)](#)

Customers Also Bought

TE Part #1676300-2
[RN 0805 30K1 0.1% 10PPM 1KRL](#)

TE Part #1676204-2
[RN 0805 16K5 0.1% 10PPM 1KRL](#)

TE Part #1676307-3
[RN 0805 33K2 0.1% 10PPM 5KRL](#)

TE Part #1676339-2
[RN 0805 42K2 0.1% 10PPM 1KRL](#)

TE Part #8-2176381-8
[RQ 0805 100K 0.1% 10PPM 5K RL](#)

TE Part #1-2176381-6
[RQ 0805 17K8 0.1% 10PPM 5K RL](#)

TE Part #2-2176381-6
[RQ 0805 22K6 0.1% 10PPM 5K RL](#)

TE Part #2-2176381-9
[RQ 0805 24K3 0.1% 10PPM 5K RL](#)



Documents

Product Drawings

RQ 0805 23K7 0.1% 10PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2176381-8_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2176381-8_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2176381-8_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.