



| General Information |                                                           |
|---------------------|-----------------------------------------------------------|
| Series              | B450                                                      |
| Dielectric          | MnO2 Tantalum                                             |
| Style               | SMD Chip                                                  |
| Description         | SMD, Molded, Low ESR, Surge Robust                        |
| Features            | Low ESR, Surge Robust                                     |
| RoHS                | Yes                                                       |
| Termination         | Tin                                                       |
| AEC-Q200            | No                                                        |
| Notes               | Obsolete. Old Part Number [Obsolete] Was B45016D1576M137. |

| Specifications        |                                                     |
|-----------------------|-----------------------------------------------------|
| Capacitance           | 150 uF                                              |
| Capacitance Tolerance | 20%                                                 |
| Voltage DC            | 16 VDC (85C), 10.72 VDC (125C)                      |
| Temperature Range     | -55/+125°C                                          |
| Rated Temperature     | 85°C                                                |
| Dissipation Factor    | 10%                                                 |
| Failure Rate          | N/A                                                 |
| Resistance            | 0.13 Ohms (100kHz)                                  |
| Ripple Current        | 1070 mAmps (25C), 963 mAmps (85C), 428 mAmps (125C) |
| Leakage Current       | 24 uA                                               |

| Dimensions |                |
|------------|----------------|
| Footprint  | 7343           |
| L          | 7.3mm +/-0.3mm |
| W          | 4.3mm +/-0.3mm |
| H          | 2.8mm +/-0.3mm |
| S          | 1.3mm +/-0.3mm |
| F          | 2.4mm +/-0.1mm |
| K          | 1.8mm TYP      |

| Packaging Specifications |            |
|--------------------------|------------|
| Packaging                | T&R, 330mm |
| Packaging Quantity       | 2800       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.