

Control module conversion kit c mechanically held lighting cont 2-wire, 24VAC	
product brand name	Class LC
design of the product	2-wire, 24VAC
product type designation	Electrically held to mechanically held conversion module
special product feature	Suitable for contactor coil voltages 277V and below. Use CPT to reduce coil voltage if line voltage is higher than 277V.
<b>General technical data</b>	
touch protection against electrical shock	finger-safe
ambient temperature [°F]	
• during storage	-22 ... +149 °F
• during operation	-13 ... +104 °F
ambient temperature	
• during storage	-30 ... +65 °C
• during operation	-25 ... +40 °C
country of origin	United States
accessories / included	Control module, latch, latch cover and auxiliary contact(s)
control voltage / at AC / rated value	24 ... 24 V
<b>Mounting/wiring</b>	
fastening method	mounted onto contactor
type of electrical connection	screw-type terminals
tightening torque [lbf-in] / with screw-type terminals	7 ... 12 lbf-in
type of connectable conductor cross-sections / for AWG cables / for control connection / with screw-type terminals / single or multi-stranded	1x (22 ... 12 AWG)
temperature / of the conductor / for control connection / with screw-type terminals / maximum permissible	75 °C
material / of the conductor	CU
<b>Certificates/ approvals</b>	
certificate of suitability	cULus
<b>Further information</b>	
Industry Mall (Online ordering system) <a href="https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:49LCCM1A">https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:49LCCM1A</a>	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) <a href="https://support.industry.siemens.com/cs/ww/en/ps/US2:49LCCM1A">https://support.industry.siemens.com/cs/ww/en/ps/US2:49LCCM1A</a>	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax_us.aspx?mlfb=US2:49LCCM1A&amp;lang=en">http://www.automation.siemens.com/bilddb/cax_us.aspx?mlfb=US2:49LCCM1A&amp;lang=en</a>	

last modified:

9/14/2022 