






REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	NEW			Zoey	2017/5/19
△	Original Model: C717-3			HUABO	2023/10/28



TECHNICAL CHARACTERISTICS

1.General Characteristics

Durability: 5,000 cycles min.

2.Electrical Characteristics

Contact resistance: Initial: 50mΩ Max.

After Test: 100mΩ Max.

Insulation resistance: >1000MΩ/500V DC

3.Solderability

IR reflow: 250°C, 5sec. Max

Manual soldering: 370°C, 3sec. Max

4.Environmental Characteristics

Operating temperature: -40°C~+85°C

Operating humidity: 10%~+95%RH



ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	BASE	1	Hi-temp Thermoplastic	Black UL94V-0
2	SHELL	1	Stainless steel	
3	DATA CONTACT	6	Copper Alloy	Contact area: Gold plated

Unless otherwise specified, other tolerance are:

X	±0.35	X'	±5'
X.X	±0.25	X.X'	±4'
X.XX	±0.15	X.XX'	±3'
X.XXX	±0.10	X.XXX'	±2'

PROJ.	UNIT	SCALE
⊕	mm	1:1

CUSTOMER DRAWING

RECOMMENDED P.C.B LAYOUT COMPONENT SIDE (TOLERANCE ±0.05)

MUP MUP INDUSTRIAL CO.,LTD.

NAME: **SIM Card Connector**

MODEL NO: **MUP-C7017-03**

TYPE: **Without post 6p**

DRAWN: Zoey May.19.2017

CHECKED: Jimmy May.19.2017

APPROVAL: Wang May.19.2017

DWG NO.: DWG-C7017-03-01

SHEET 1/1

REVISION 2