

YASHIN POWER, Longhua District, Shenzhen,
Guangdong 518108, P. R. China
TEL: 17666139630

客户承认书

SPECIFICATION FOR APPROVAL

CUSTOMER/客户: _____

CUSTOMER P.N./客户物料号: _____

MODEL NO./产品型号: **S-360-36**

PRODUCT NO./产品编号: **开关电源 360W 36V/10A**

SAMPLE DATE/送样日期: **2024-1-26**

CUSTOMER AUTHORIZED SIGNATURE/客户承认签核		

Please return to us one copy of “SPECIFICATION FOR APPROVAL” with
you approved signature./客户确认签字，盖章后请回传一份承认书给我
司。

拟 制:	安规工程师:	项目工程师:	批 准:

** Table Of Content/目录 **

1. Functional description/功能描述.....	3
2. SCOPE/简述.....	3
2.1. Description/产品类型.....	3
3. Input Characteristics/输入特性	3
3.1. Input Voltage & Frequency/输入电压与频率	3
3.2. Input AC Current/AC 输入电流.....	3
3.3. Inrush Current (cold start)/浪涌电流(冷启动).....	4
3.4. Type Efficiency/典型效率.....	4
3.5. Energy Consumption /空载功耗	4
4. Output Characteristics/输出特性.....	4
4.1. Static Output Characteristics <Vo & R+N>/静态输出特性	4
Line/ Load Regulation/线性/负载调整	
4.2. 率	4
4.3. Turn - on Delay Time/开机延迟时间	4
4.4. Hold-up Time/关机维持时间.....	4
4.5. Rise Time/上升时间.....	4
4.6. Fall Time/下降时间.....	4
4.7. Output Overshoot / Undershoot/输出过冲/欠冲.....	4
4.8. Output Load Transient Response/输出负载瞬态响应.....	5
5. Protection Requirements/保护要求.....	5
5.1. Over Current Protection/过流保护.....	5
Short Circuit Protection/短路保	
5.2. 护	5
5.3. Over Voltage Protection/过压保护	5
Over temperature protection/过温保	
5.4. 护	5
6. Environment Requirements/环境要求	5
6.1. Operating Temperature and Relative Humidity/操作温/湿度要求.....	5
6.2. Storage Temperature and Relative Humidity/存储温/湿度要求	5
Sea level shall be low 2.000 meters/低于 2000	
6.3. 米.	5
6.4. Vibration/振动	5
7. Reliability Requirements/可靠性要求	6
Burn-in/老	
7.1. 化	6
7.2. E-caps lifetime	7
7.3. MTBF :	7
EMI/EMS Standards/EMI/EMS 标	
8. 准	7
EMI Standards/EMI 标	
8.1. 准	7
8.2. EMS Standards/EMS 标	8

准	
9. Safety Standards/安规标准	8
10. Mechanical Outline Drawing/外观示意图	9

1. Functional description/功能描述

S-360-36 是一款 **360W** 36V 输出电源供应器, 输入电压范围 **100~264Vac** (拨码开关切换)。输出电压为 36V, 峰值**效率高达 88%**; 采用铝外壳设计且具有很好的散热效果。该电源具有多种保护功能, 如输入欠压保护、输出过流保护、输出过压保护、**输出短路保护功能**; 符合 **EN61000-3-2** 谐波要求; 为各种工程应用提供了一个高性能和高性价比的解决方案。

2. SCOPE/简述

The document detail the electrical, mechanical and environmental specifications of a SMPS, the power supply provide 360W continuous output power.

资料详细描述了一款 **360W** (连续输出功率)开关电源的电气性,结构性及环境等要求。

The power supply shall meet the **RoHS** requirement.

此款电源符合 **RoHS** 要求。

2.1. Description/产品类型

SMPS Adaptor(Wall mount)/插墙式适配器

SMPS Adaptor(Desk-top)/桌面型适配器

Open Frame/开放式结构

 SMPS Unit (With Case)/导轨型

Others/其他

3. Input Characteristics/输入特性

3.1. Input Voltage & Frequency/输入电压与频率

The range of input voltage is from 100Vac to 264Vac single phase, switching the input voltage through a switch.

输入电压范围: 从 **200Vac** 到 **264Vac**, 单相输入,通过开关切换输入电压。

Items	Min/最小	Nom/额定值	Max/最大
Input Voltage/输入电压	100 Vac	240 Vac	264 Vac
Input Frequency/输入频率	47 Hz	50~60 Hz	63 Hz

3.2. Input AC Current/AC 输入电流

Input Voltage/输入电压	100Vac	230Vac	Full load
Input AC Current/AC 输入电流	6.5A Max	3A Max	Full load

3.3. Inrush Current (cold start)/浪涌电流(冷启动)

The energy of inrush current should not be over the I^2T of fuse & bridge diodes.

冷启动时, 浪涌能量不能超过整流桥和保险丝的 I^2T , 且不能有损坏。

3.4. Type Efficiency/典型效率

86% min.(average efficiency). @110Vac/60Hz input .

88% min.(average efficiency).@230Vac/50Hz input.

输入电压 **200V/60Hz** 时, 平均效率不低于 **86%**。

输入电压 230V/50Hz 时, 平均效率不低于 88%。

3.5. Energy Consumption /空载功耗

No load Consumption $\leq 3W(230Vac/50Hz)$.

在额定输入 230Vac/50Hz 时,空载功耗 $\leq 3W$ 。

4. Output Characteristics/输出特性

4.1. Static Output Characteristics <Vo & R+N>/静态输出特性

Output	Rated Load/额定负载		Output Range	R+N	Remark
Rate	Min. Load	Rate.Load	输出电压范围	纹波与噪声	备 注
36V	0.0A	10A	34.28V ~ 37.8V	300mVp-p	

Ripple & Noise: Measurement is done by 20MHz bandwidth oscilloscope and the output paralleled a 0.1uF ceramic capacitor and a 10uF electrolytic capacitor. (test under the condition of rated input and rated output).

纹波与噪声: 量测时示波器选用 20MHz 带宽限制,输出端要并联一颗 0.1uF 的陶瓷电容和一颗 10uF 的电解电容。(在额定输入及输出的条件下检测)。

4.2. Line/ Load Regulation/线性/负载调整率

Output	Load Condition/负载条件		Line Regulation	Load Regulation	Remark
Rate	Min. Load	Rate.Load	线性调整率	负载调整率	备 注
36V	0.0A	10A	$\pm 3\%$	$\pm 3\%$	

4.3. Turn - on Delay Time/开机延迟时间

3S max. @180Vac to 230Vac input & Full load.

输入电压 180Vac to 230Vac 满载时, 开机延迟时间不超过 3S。

4.4. Hold-up Time/关机维持时间

10mS min. @ Full load &180Vac/60Hz input turn off at worst case.

输入电压 180Vac/60Hz 满载时, 关机时间最差情况不小于 10 毫秒。

10mS min. @ Full load &230Vac/50Hz input turn off at worst case.

输入电压 230Vac/50Hz 满载时, 关机时间最差情况不小于 10 毫秒。

4.5. Rise Time/上升时间

80 mS max. @ Full load &180Vac/60Hz and 230Vac/50Hz input.

在 180Vac/60Hz 和 230Vac/50Hz 输入满载时, 上升时间不超过 80 毫秒。

4.6. Fall Time/下降时间

30 mS max. @ Full load.

满载时, 下降时间不超过 30 毫秒。

4.7. Output Overshoot / Undershoot/输出过冲/欠冲

10 % max. When the power on or off, when it is the full input voltage and full load.

开关机时, 输出过冲/欠冲均不大于 10%。

4.8. Output Load Transient Response/输出负载瞬态响应

Output voltage within 34.28V ~ 37.8V for load step from 25% to 50% to 25%,50% to 75% to 50% R/S: 0.25A/uS, Transient Response Recovery Time :200uS, Dynamic response overshoot 10%.

输出电压在 34.28V ~ 37.8V 之间,负载变化: 从 25% to 50% to 25%, 50% to 75% to 50%斜率: 0.25A/uS, 动态响应恢复时间: 20mS, 动态响应过冲 $\pm 10\%$ 。

5. Protection Requirements/保护要求

5.1. Over Current Protection/过流保护

Over Power Point Limited: 105%~150% Full load (@100/230Vac)

过流保护点限制:105%~150% 满载 (100~230Vac)

The output shall hiccup when the over current applied to the output rail, and shall

be self-recovery when the fault condition is removed.

当过流作用于输出时, 输出打嗝, 当故障情况消除时, 自动恢复。

5.2. Short Circuit Protection/短路保护

The input power shall decrease when the output short.the power supply shall no

damage, and shall be auto-recovery when the fault condition is removed.

当输出短路时, 输入功率应减小。电源不应损坏, 故障排除后重新启动恢复。

5.3. Over Voltage Protection/过压保护

In the case of 100 ~ 264Vac input space time load and full load,32V < OVP < 38V, and

can not be damaged.

在 100~264Vac 输入时空载和满载情况下, 输出过压保护大于 32,小于 38V, 且不能损坏。

5.4. Over temperature protection/过温保护

When the temperature exceeds 110±5℃, turn off the output voltage and

automatically recover when the temperature drops to 75℃.

当温度超过 110±5℃时, 关闭输出电压, 温度下降到 75℃后自动恢复。

6. Environment Requirements/环境要求

6.1. Operating Temperature and Relative Humidity/操作温/湿度要求

Operating temperature:-30℃ to +70℃

工作温度: -30℃ to +70℃

Operating Relative humidity:10%RH to 90%RH

工作湿度: 10%RH to 90%RH

6.2. Storage Temperature and Relative Humidity/存储温/湿度要求

Storage Temperature:-40℃ to +80℃

储存温度: -40℃ to +85℃

Storage relative humidity:10%RH to 95%RH non-condensing

存储湿度: 10%RH to 95%RH

6.3. Sea level shall be low 2.000 meters/低于 2000 米.

6.4. Vibration/振动

10 to 500Hz sweep at a constant acceleration of 2.0G(Displacement amplitude:

3.5mm),10 minutes per cycle, 60 minutes on the X, Y and Z axis.

以 2.0G 恒定加速度(位移幅值:3.5mm)扫频 10 - 500Hz, 每循环 10 分钟, X、Y、Z 轴 60 分钟。

7. Reliability Requirements/可靠性要求

7.1. Burn-in/老化

The power supply shall be burn-in for 2 Hours under rated input and 80% Full load at 40℃

±5℃.

电源在 40℃±5℃额定输入、80%满负荷情况下老化 2 小时。

7.2. E-caps lifetime

The E-caps used in this power supply must be with lifetime of 3 years @ 25℃ of full load. @ 100Vac / 60Hz and / or 240Vac / 50Hz.

本电源使用的电解电容寿命必须在 25℃满负荷时使用寿命为 3 年。@ 200Vac / 60Hz 和/或 240Vac / 50Hz。

7.3.MTBF :

≥200 K Hrs MIL-HDBK-217F (25℃).

平均无故障时间 20 万小时以上，标准 MIL-HDBK-217F (25℃)。

8. Safety Standards/安规标准

8.1. Dielectric Strength(Hi-pot)/介电耐压强度(高压)

I/P- O/P: 3KVac / 5mA max. / 60 second .

输入对输出: 3KVac / 5mA max. / 60 秒.

I/P-FG: 2KVac / 5 mA max. / 60 second .

输入对地: 2KVac / 5 mA max. / 60 秒

O/P-FG: 0.5K Vac / 5 mA max. / second.

输出对地: 0.5KVac / 5 mA max. / 60 秒.

8.2. Leakage Current/漏电流

3.5mA max. at 250Vac / 50Hz.

输入 250V AC,漏电流小于 3.5mA。

8.3. Insulation Resistance/绝缘阻抗

I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25℃/ 70% RH

输入对输出、输入对地、输出对地，在 25℃ 70%的湿度分别施加 500Vdc 进行测试，阻抗大于 100 兆欧姆。

9. Mechanical Outline Drawing/外观示意图

单位: 215*115*50mm

