

**2388280-7**

✓ ACTIVE

**AMP | Heavy Duty Sealed Connector Series**

TE Internal #: 2388280-7

Other Automotive Connector Accessories, Slide, PA6 GF, Gray, -40

– 140 °C [-40 – 284 °F]

[View on TE.com >](#)

Connectors &gt; Automotive Connectors &gt; Automotive Connector Accessories &gt; Other Automotive Connector Accessories &gt;

Heavy Duty Sealed Connector Series Fixing Slides

Automotive Connector Accessory Type: **Slide**Primary Product Material: **PA6 GF**Primary Product Color: **Gray**Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**[All Heavy Duty Sealed Connector Series Fixing Slides \(33\)](#)

## Features

### Product Type Features

Automotive Connector Accessory Type      **Slide**

### Body Features

Primary Product Material      **PA6 GF**Primary Product Color      **Gray**

### Usage Conditions

Operating Temperature Range      **-40 – 140 °C [-40 – 284 °F]**

### Industry Standards

UL Flammability Rating      **UL 94V-0**

## Product Compliance

For compliance documentation, visit the product page on [TE.com >](#)EU RoHS Directive 2011/65/EU      **Compliant**EU ELV Directive 2000/53/EC      **Compliant**

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023  
(235)

Candidate List Declared Against: JUNE  
2023 (235)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per  
homogenous material. Also BFR/CFR/PVC  
Free

Solder Process Capability

Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




TE Part # CAT-H3399-CH8172

Heavy Duty Sealed Connector Series  
Housings


## Also in the Series | Heavy Duty Sealed Connector Series




Automotive Connector Caps & Covers  
(25)



Automotive Housings(207)




Connector Seals & Cavity Plugs(5)



Data Connectivity Headers(2)



Data Connectivity Housings(18)



Other Automotive Connector Accessories(34)



PCB Headers &amp; Receptacles(1)

## Documents

### Product Drawings

#### SLIDE,TAB HSG ASSY, GROUP E

English

---

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2388280-7\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2388280-7\\_A.3d\\_jgs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2388280-7\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

#### Application Specification

English