



- [Circuit Board Indicators](#)
- [Panel Mount Indicators](#)
- [Solid State Lighting](#)
- [Traffic Signals](#)
- [Vehicle Lighting](#)
- [Rail](#)
- [Obstruction Lighting](#)
- [Hazardous Area Lighting](#)
- [Heliport Lighting](#)

- how to purchase
- [sales contacts](#)
 - [stock check](#)

search

Product Line Search

Please select a Product Line to search.

Part # / Text Search

Part No.:

Text Search:

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
[FAQs](#)

Dialight Ltd (UK)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)

| Circuit Board Indicators - Through Hole Indicators | |
|--|--------------------------------|
| P/N# 5640710555F | 3 mm Lens |
| Description | 3 mm Tri-Level CBI R/Y-R/Y-R/Y |
| Package Options | 5 Pieces Per Bag |
| Product Type | Through Hole Indicators |
| Sub Product Type | with Tri-Level Housing |
| Configuration | 3 mm Lens |
| Viewing | Right Angle |
| Viewing Angle | 45 |
| Test Current (mA) | 20mA |
| Absolute Maximum Ratings (Ta = 25 °) | |
| Solder Temp | 260Å° for 5 sec |
| Operating Temp | -55 to +100° C |
| Storage Temp | -55 to +100° C |

[Data Sheet](#) [view/download](#) [RoHS / pB Free](#) [view PDF](#)

Distributor Stock Check

Check stock with our distributors now.

| Operating Characteristics | | |
|----------------------------|-------------------------|-------------------------|
| | Found in position(s): 1 | Found in position(s): 2 |
| LED Position | | |
| Color | Red | Yellow |
| Lamp Type | Bi-Color | Bi-Color |
| LED Type | | |
| Intensity Min (mcd) | 1.7 | 1.7 |
| Intensity Typ (mcd) | 5.6 | 5.6 |
| Intensity Max (mcd) | | |
| Fwd Voltage Min | | |
| Fwd Voltage Typ | | |
| Fwd Voltage Max | | |
| Dom Wavelength Min (nm) | | |
| Dom Wavelength Typ (nm) | | |
| Dom Wavelength Max (nm) | | |
| Power Dissipation Max (mW) | 100 | 60 |
| Backlighting | | |
| Pitch Between Vertical | | |
| Pitch Between Horizontal | | |
| Lum Intensity Min | | |
| Lum Intensity Typ | | |
| Lum Intensity Max | | |