



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **High Value/High Voltage Resistor**

Number of Terminations: **2**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **5 %**

Element Type: **Metal Film**

Features

Product Type Features

Resistor Type	High Value/High Voltage Resistor
Element Type	Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	5 %
Resistance Class	1k $\Omega$ – 1M $\Omega$
Resistance Value	270K $\Omega$
Power Rating	2 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

--	--



Product Height	5 mm[.197 in]
Product Length	10.5 mm[.413 in]
Product Width	5.5 mm[.217 in]

Usage Conditions

Temperature Coefficient	$\pm 200$ ppm/ $^{\circ}\text{C}$
-------------------------	-----------------------------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMV2W270KJT

270K  $\Omega$ , Metal Film, High Value/High Voltage Resistor, 5 %, 2 Termination, Taped & Reeled, 2 W,  $\pm 200$  ppm/ $^{\circ}\text{C}$ , Solder, Height .197 in [5 mm], CGS SMV



TE Part # 2176322-5  
SMV 1W 220K 5%

TE Part # 2176322-8  
SMV 1W 390K 5%

TE Part # 2-2176323-5  
SMV 2W 10M 5%

TE Part # 2176323-9  
SMV 2W 470K 5%

TE Part # 2176324-1  
SMV 3W 100K 5%

TE Part # 7-2176619-1  
SMQF2W 270K 5%

Also in the Series | CGS SMV

Surface Mount Resistors(75)

Customers Also Bought

TE Part #316090-1  
2.5 SIGNAL D/LOCK CAP HSG 6P

TE Part #917686-1  
2.5 SIGNAL D/LOCK PLUG HSG 2P

TE Part #5525DSO-DB001DS  
1PSID DIGITAL PRESSURE SENSOR

TE Part #2071366-2  
EW60-1A3-CL12D04,00000

TE Part #61188-1  
250 FASTON FLAG REC 16-12 AWG  
TPBZ

TE Part #4-2176347-3  
CRGCQ 2010 33K 1%

TE Part #DT15-4P  
HDR, 4P, GRY, ST, NI/CU

TE Part #1318747-1  
025 ECU PLUG HSG ASSY 32P

SMV2W270KJT

270K  $\Omega$ , Metal Film, High Value/High Voltage Resistor, 5 %, 2 Termination, Taped & Reeled, 2 W,  $\pm 200$  ppm/ $^{\circ}\text{C}$ , Solder, Height .197 in [5 mm], CGS SMV



Documents

Product Drawings

SMV 2W 270K 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2176323-6\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2176323-6\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2176323-6\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Metal glaze High Voltage SMD Resistor Type SMV series

English