

APPLICABLE STANDARD		SPECIFICATIONS															
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾													
	VOLTAGE	100 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %													
	CURRENT	0.5 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾													
CONSTRUCTION																	
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×												
MARKING	CONFIRMED VISUALLY.				×												
ELECTRIC CHARACTERISTICS																	
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).		40 mΩ MAX.		×												
CONTACT RESISTANCE	20 mV MAX, 1 mA(DC OR 1000Hz)		50 mΩ MAX.		×												
MILLIVOLT LEVEL METHOD																	
INSULATION RESISTANCE	250 V DC		100 MΩ MIN.		×												
VOLTAGE PROOF	300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		×												
MECHANICAL CHARACTERISTICS																	
MECHANICAL OPERATION	100 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×												
VIBRATION	FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×												
SHOCK	490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				×												
ENVIRONMENTAL CHARACTERISTICS																	
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 hrs.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×												
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-55→+15~+35→ +85→+15~+35°C TIME 30 → MAX 5 → 30 → MAX 5 min 5 CYCLES.				×												
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO HEAVY CORROSION.		×												
HYDROGEN SULPHIDE	EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA 38)				×												
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		×												
	2) SOLDERING IRONS : 360 °C, FOR 5 s				×												
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 240±3°C, FOR IMMERSION DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.		×												
REMARK																	
⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.		<table border="1"> <tr> <td>APPROVED</td> <td>HS.OKAWA</td> <td>06.01.25</td> </tr> <tr> <td>CHECKED</td> <td>HS.OZAWA</td> <td>06.01.25</td> </tr> <tr> <td>DESIGNED</td> <td>KY.NAKAMURA</td> <td>06.01.25</td> </tr> <tr> <td>DRAWN</td> <td>TK.YANAGISAWA</td> <td>05.09.09</td> </tr> </table>		APPROVED	HS.OKAWA	06.01.25	CHECKED	HS.OZAWA	06.01.25	DESIGNED	KY.NAKAMURA	06.01.25	DRAWN	TK.YANAGISAWA	05.09.09		
APPROVED	HS.OKAWA	06.01.25															
CHECKED	HS.OZAWA	06.01.25															
DESIGNED	KY.NAKAMURA	06.01.25															
DRAWN	TK.YANAGISAWA	05.09.09															
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-084968-23												
	SPECIFICATION SHEET		PART NO.	FX6-60P-0.8SV (93)													
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL576-0005-4-93	1/1												