

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾		
	VOLTAGE	50 V AC		OPERATING HUMIDITY RANGE	95 % RH MAX. (NO DEW CONDENSATION IS PERMITTED)		
	CURRENT	0.3 A					
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×
MARKING		CONFIRMED VISUALLY.				×	×
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		60 mΩ MAX.		×	
INSULATION RESISTANCE		100 V DC		100 MΩ MIN.		×	
VOLTAGE PROOF		150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		×	×
MECHANICAL CHARACTERISTICS							
INSERTION AND WITHDRAWAL FORCE		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE: 72 N MAX. WITHDRAWAL FORCE: 3.0 N MIN.		×	
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 70 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE : 0.75 mm, WITH 10 CYCLES IN 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms, 3 TIMES IN 3 DIRECTIONS.				×	
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 70 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.		×	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE: -55 → +15 ~ +35 → +85 → +15 ~ +35 °C TIME 30 → 2 ~ 3 → 30 → 2 ~ 3 min. UNDER 5 CYCLES.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
DRY HEAT		EXPOSED AT 85 °C, 96h.		① CONTACT RESISTANCE: 70 mΩ MAX.		×	
COLD		EXPOSED AT -55 °C, 96h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		NO HEAVY CORROSION.		×	
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS C 0090)		① CONTACT RESISTANCE: 70 mΩ MAX. ② NO HEAVY CORROSION.		×	
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s		NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.		×	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 240°C, FOR IMMERSION DURATION, 3 sec.		NO PINHOLE OR DEWETTING ON SOLDERED SURFACE.		×	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED		CHECKED	DATE
△							
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.				APPROVED	HS. OKAWA	06.04.18	
				CHECKED	HS. OZAWA	06.04.18	
				DESIGNED	KT. DOI	06.04.17	
Unless otherwise specified, refer to JIS C 5402.				DRAWN	KT. DOI	06.04.17	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-151969-25	
HRS	SPECIFICATION SHEET			PART NO.	FX10A-120P-SV1 (71)		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL570-0142-7-71 △ 1/1		