



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Power Resistor**
Number of Terminations: **2**
Package Size Code: **1206**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **1 %**

Features

Product Type Features

Resistor Type	Power Resistor
Package Size Code	1206
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	100 V
Passive Component Tolerance	1 %
Resistance Class	1k Ω – 1M Ω
Resistance Value	8.87K Ω
Power Rating	2 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder



Dimensions

Product Height	.43 mm[.017 in]
Product Length	3.05 mm[.12 in]
Product Width	1.55 mm[.061 in]

Usage Conditions

Operating Temperature Range	-55 – 155 $^{\circ}\text{C}$
Temperature Coefficient	± 50 ppm/ $^{\circ}\text{C}$

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 1-2176525-8


3503G 2B 8K87 1% 1K RL

Also in the Series | CGS 3503



Surface Mount Resistors(534)


Customers Also Bought





TE Part #T4061320003-005


M8 CABLE ST FEMALE 5M 3POS PUR CABLE





TE Part #2842124-3


3P,2MM,BRK HDR,SRRT,2.8,0.76AU, BOX





TE Part #2314928-3


3P,2MM,B-B,REC,SRHZ,2.1,0.1AU,TB





TE Part #8-2176369-9


RQ 0603 332R 0.1% 10PPM 5K RL





TE Part #4-2176391-3


RQ 1206 34K 0.1% 10PPM 5K RL





TE Part #2331928-5


SCL 1.0 HDR DRV T USP 010 SMT G1 TBK





TE Part #5-2176480-2


RA73F 1J 1K87 0.1% 5K RL





TE Part #2-2176582-2


RLC73PD 2B 1R0 1% 5K RL





TE Part #6-2176581-6

RLC73PD 2B R267 1% 5K RL





TE Part #2176582-1

RLC73PD 2B R604 1% 5K RL



Documents

Product Drawings

3503G 2B 8K87 1% 5K RL

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-2176528-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2176528-8_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-2176528-8_A.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Aluminium Nitride Thin Film Power Resistor - Type 3503 Series

English