



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**
Number of Terminations: **2**
Package Size Code: **1210**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **1 %**

[All Thick Film Resistor: Current Sense \(796\)](#)

Features

Product Type Features

Resistor Type	Current Sensing Resistor
Package Size Code	1210
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	1 %
Resistance Class	Up to 1k Ω
Resistance Value	33 Ω
Power Rating	.5 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.1 mm[.122 in]



Product Width	2.6 mm[.102 in]
---------------	-----------------

Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RL73H2ER33FTDF

33 Ω , Thick Film, Current Sensing Resistor, 1 %, 2 Termination, 1210, Taped & Reeled, .5 W, ± 100 ppm/ $^{\circ}\text{C}$, Solder, Height .022 in [.55 mm], CGS RL73





TE Part # CAT-C339-R529
Thick Film Resistor: Current Sense



TE Part # 6-1622824-1
RL73N 1J R10 5% 5K RL

Also in the Series | CGS RL73



Surface Mount Resistors(856)

Customers Also Bought



TE Part #5-1462037-5
IM41JR=IM RELAY 100mW 3V BIS



TE Part #1623730-4
BCHE 4 W 15R 5%



TE Part #T4145515041-001
M12 R/A F PNLREAR STAMPED PIN D-CODE 4P



TE Part #3-1415379-1
RT33LA24



TE Part #2-1624112-4
3650 0402 27nH 5% 2K RL



TE Part #4-1624112-8
3650 0402 22nH 5% 2K RL



TE Part #8-1625890-2
2W SM M/OX 5% 560K



TE Part #5-2176349-5
CRGCQ 2512 330K 1%



TE Part #3-2176350-4
CRGCQ 2512 330K 5%



TE Part #4-1879207-9
RN 0603 487K 0.1% 10PPM 1K RL



Documents

Product Drawings

RL73H 2E R33 1% 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1879463-7_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1879463-7_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1879463-7_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English