



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Number of Terminations: **2**

Package Size Code: **0603**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **.1 %**

Features

Product Type Features

|                   |                    |
|-------------------|--------------------|
| Resistor Type     | Precision Resistor |
| Package Size Code | 0603               |
| Element Type      | Thin Film          |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

|                             |                   |
|-----------------------------|-------------------|
| Operating Voltage           | 75 V              |
| Passive Component Tolerance | .1 %              |
| Resistance Class            | Up to 1k $\Omega$ |
| Resistance Value            | 64.9 $\Omega$     |
| Power Rating                | .15 W             |

Termination Features

|                                         |        |
|-----------------------------------------|--------|
| Number of Terminations                  | 2      |
| Surface Mount Resistor Termination Type | Solder |



Dimensions

|                |                  |
|----------------|------------------|
| Product Height | .45 mm[.018 in]  |
| Product Length | 1.55 mm[.061 in] |
| Product Width  | .8 mm[.031 in]   |

Usage Conditions

|                         |            |
|-------------------------|------------|
| Temperature Coefficient | ±10 ppm/°C |
|-------------------------|------------|

Packaging Features

|                  |                |
|------------------|----------------|
| Packaging Method | Taped & Reeled |
|------------------|----------------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Reflow solder capable to 260°C                                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2176372-6  
RQ 0603 56K2 0.1% 10PPM 5K RL

TE Part # 2176371-8  
RQ 0603 5K49 0.1% 10PPM 5K RL

TE Part # 3-2176382-0  
RQ 0805 267K 0.1% 10PPM 5K RL

TE Part # 3-2176389-4  
RQ 1206 237R 0.1% 10PPM 5K RL

TE Part # 4-2176391-2  
RQ 1206 33K2 0.1% 10PPM 5K RL

TE Part # 2-2176365-1  
RQ 0603 64R9 0.1% 10PPM 1K RL

Also in the Series | **Holsworthy RQ73**

Surface Mount Resistors(3078)

Customers Also Bought

TE Part #282837-6  
TERMI-BLOK PCB MOUNT 6P

TE Part #9-1676481-7  
CPF 0603 91K 0.1% 25PPM 1K RL

TE Part #7-1879140-7  
RN 0603 115K 0.1% 10PPM 5K RL

TE Part #1-1337452-0  
BNC Ins BHSkt 50Ohm Nickel Gol

TE Part #4-2176087-5  
RP 1J 0.166W 196R 0.1% 25PPM 1K RL

TE Part #2-2176370-1  
RQ 0603 698R 0.1% 10PPM 5K RL

TE Part #1-2176381-0  
RQ 0805 15K4 0.1% 10PPM 5K RL

TE Part #7-2176378-8  
RQ 0805 63R4 0.1% 10PPM 5K RL





TE Part #1-1337433-0  
BNC RM BHJ Hex 50Ohm Nickel Pltd  
RG58C/U



TE Part #ADP-SMAM-SMAM-G  
SMA Plug to SMA Plug

Documents

Product Drawings

RQ 0603 64R9 0.1% 10PPM 5K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-2176369-1\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-2176369-1\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-2176369-1\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.