

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	100 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %	
	CURRENT	0.4 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING		CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).	45 mΩ MAX.	×	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1 mA(DC OR 1000Hz)	55 mΩ MAX.	×	—
INSULATION RESISTANCE		250 V DC	100 MΩ MIN.	×	—
VOLTAGE PROOF		300 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 55 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, 2 h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 55 mΩ MAX.	×	—
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms FOR 3 TIMES IN 3 DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 55 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN.	×	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15~+35→ +85→+15~+35°C TIME 30 → 2~3 → 30 → 2~3 min 5 CYCLES.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 55 mΩ MAX. ② NO HEAVY CORROSION.	×	—
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD: JEIDA 38)		×	—
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 240°C, FOR IMMERSION DURATION, 3 s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED. Unless otherwise specified, refer to JIS C 5402.			APPROVED	HS.OKAWA	05.11.24
			CHECKED	HS.OZAWA	05.11.24
			DESIGNED	TK.YANAGISAWA	05.11.22
			DRAWN	TK.YANAGISAWA	05.11.22
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-150569-25
	SPECIFICATION SHEET		PART NO.	FX8-60P-SV1 (71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL578-0041-0-71	△ 1/1