

Product Features

1.

2 pads SMD glass sealed crystal
2.

Reliable glass sealed ceramic package
3.

Wide operating temperature range
4.

Superior and reliable performance in harsh environment
5.

AEC-Q200 Compliant
6.

Contains Pb in sealing glass exempted by RoHS directive
7.

Industry Standard Package :
5.0*3.2*1.25 mm (AA Series)

- Application :
- Automotive Ethernet
- In-Vehicle Infotainment system
- Battery Management System , Body Control
- Instrument clusters
- Power steering , Breaking System , Engine Control



● Table 1 . Electrical Specifications

Test condition


Ambient temperature : 25 ± 5°C

Relative humidity : 40% ~ 70%

Parameters	Symbol	Min.	Typ.	Max.	Units	Notes
Nominal Frequency	F	7.2 ~ 48			MHz	
Frequency Tolerance	FT	± 10			ppm	@25°C±3°C
Frequency Stability Over Operating Temp. Range (Reference 25°C)	ST	± 15			ppm	@-40~85°C
		± 30				@-40~105°C
		± 50				@-40~125°C
		± 150				@-40~150°C
Operating Temperature	Topr	-40	25	150	°C	
Load Capacitance	CL	8 , 10 , 12 or specify			pF	
Drive Level	DL	-	100	300	uW	
Equivalent Series Resistance	ESR	-	-	150	Ohm	7.2~12MHz
		-	-	100		12~20MHz
		-	-	50		20~48MHz
Aging	-	± 3			ppm	1st Year
		± 15				15th Year

Note : The table shows common spec. if you have special spec. requirement , please feel free to contact our salesperson.

● Dimensions



(Unit : mm)