



Sensors > Temperature Sensors > RTD Sensors > RTD Sensor Elements



RTD Element Type: **Platinum Glass Wire Wound Element**

Tolerance Class: **Class B / W0.3**

Element Package: **Glass**

Element Material: **Platinum**

Lead Wire Style: **Ni/Pt**

Features

Product Type Features

Wire/Cladding Type	Ni/Pt
Model Number	GO 1327
RTD Element Type	Platinum Glass Wire Wound Element
Element Material	Platinum
Lead Wire Style	Ni/Pt

Configuration Features

Connector Type	Open Ends
----------------	-----------

Dimensions

Wire Length	15 mm
Diameter (Body)	2.7 mm[.106 in]
Wire Diameter	.25 mm[.009 in]
Length (Body)	13 mm[.51 in]

Usage Conditions

Resistance (at T_ref)	100 (0 °C) Ω
T_ref for Accuracy	0 °C
Ambient Temperature Range	-196 – 400 °C[-320.8 – 752 °F]
T1 and T2 for TCR	0 and +100 °C
TCR at (T1 and T2)	3850 ppm/°C



Accuracy (at T_ref)	± .3 °C
T_ref for Resistance	0 °C
Maximum Temperature	400 °C[752 °F]

Packaging Features

Element Package	Glass
-----------------	-------

Other

Tolerance Class	Class B / W0.3
Wire Count	2

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # SB0866

GO1327 1Pt100 W0.15 L13/D2.7mm

Also in the Series | MEAS GO



RTD Sensor Elements(10)

Customers Also Bought




TE Part #1478762-9

METAL BACKSHELL 9 WAY TOP E



TE Part #726343-1

SO-RINGZUNGE D46234



TE Part #966067-4

FER,WIRE,PL SLV,.75/18,L6,GREY,LP




TE Part #353293-9

MINI CT MT REC ASSY 9P GRAY



TE Part #2238177-1

187 X 032 POS LOC REC 20-16 NISTL



TE Part #9154853001

FLT0111-0.50-0



TE Part #2180143008

55A0811-20-9




TE Part #7-2176367-1

RQ 0603 24K9 0.1% 10PPM 1K RL



TE Part #803797-000

SRFR-4/2.9-8-RSU-1M



TE Part #32208548

SONDE CM\_ M\_ \_\_\_\_ 222\_\_ 1PT



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_SB0865\_1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_SB0865\_1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_SB0865\_1.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

GWW Type GO

English