

Connectors > Circular Connectors > Standard Circular Connectors



Sealable: No

Contact Current Rating (Max): 75 A

Circuit Application: Power

Shell Base Material: Brass

Circular Connector Shell Size: 40

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass
---------------------	-------

Contact Features

Contact Current Rating (Max)	75 A
Circular Connector Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Circular Connector Shell Size	40
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles
-------------------	------------

Circuit Application

Power

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

SVHC > Threshold:

Pb (1.6% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CSA263F53450001000
940 PLUG



TE Part # C0-0008-000-000
CRIMPING TOOL LARGE



TE Part # C0-0236-000-000
DIGITAL CRIMPING TOOL, MID SIZE



TE Part # C0-0313-000-000
CRIMPING DEVICE HC20 IN CASE



TE Part # C0-0010-000-000
POSITIONING INSERT FOR 3.6 MM
CONTACTS

Customers Also Bought



TE Part #60-0199-080-000
BANDOLEER CONTACT SOCKET
1MM, 7000PCS ROL



TE Part #61-0021-011-000
CONTACT PIN 2 MM



TE Part #61-0039-011-000
CONTACT PIN 3.6 MM



TE Part #ASA021N00700235000
623 PLUG



TE Part #ASA021N00700235042
623 PLUG, DELIVERY AS INDIVIDUAL
PARTS



TE Part #ASA558N00730266000
623 PLUG




TE Part #BDA107N00000150000
923 BULKHEAD CONNECTOR



TE Part #11-0586-002-000
623 extension housing IG3



TE Part #61-0172-080-027
BANDOLEER CONTACT PIN 1MM,
380 PCS ROL



TE Part #AKA384N0042035K000
627 EXTENSION, 26-PIN

Documents

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_60-0227-011-000_A.2d_dxf.zip](#)

English

[Customer View Model](#)

[ENG_CVM_CVM_60-0227-011-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60-0227-011-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Contact Socket 3.6 60-0227-011-000](#)

English