



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.


REVISIONS						
P	LTR	DESCRIPTION	DATE	OWN	APVD	
	B	REVISED PER ECO-17-007896	08AUG2017	JDS	JDS	
	B1	REVISED PER ECO-20-001920	10FEB2020	NRS	NRS	
	C	REVISED PER ECN-22-160264	22JUN2022	FC	BC	
	C1	REVISED PER ECN-22-181824	19SEP2022	GB	CB	





KEY CODE A
SCALE 4:1




KEY CODE B
SCALE 4:1







TOP VIEW OF
2292937-1 SHOWN




SECTION A - A



FRONT VIEW OF
2292937-1 SHOWN




WIRE CRIMP DIMENSIONS



INSULATION CRIMP DIMENSIONS

125°C 		1718350 0.50mm ² - 0.75mm ² (INCLUDES #20 AWG)			(2.05)
		1718348 0.25mm ² - 0.35mm ² (INCLUDES #22 AWG)			(1.85)
MAX TEMP	TERMINAL PLATING	MALE TERMINAL P/N WIRE SIZE	W.C.H	W.C.W	I.C.D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 200C12015 J MCNEAL CHW 230C12015 J SANDBURG D KLEIN 12JAN2016		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME INLINE CAP ASSEMBLY 2 POSITION, SEALED	
		APVD PRODUCT SPEC 108-151045 APPLICATION SPEC 114-151045		SIZE A1	
MATERIAL - - -		FINISH - - -		CASE CODE -	
		WEIGHT 5.9 g		DRAWING NO C=2292937	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV C	