

Features

- $R_{DS(ON)} \leq 52m\Omega @ V_{GS} = -10V$
- $R_{DS(ON)} \leq 87m\Omega @ V_{GS} = -4.5V$
- High-speed switching
- Drive circuits can be simple
- Parallel use is easy


HF

Typical Applications


- Power Management in Note Book
- Switching Application
- Battery Powered System
- Load switch

Mechanical Data


- Case: SOT-23, SOT-23-3L
- Molding Compound, UL Flammability Classification Rating 94V-0
- Terminals: Matte Tin Plated Leads, Solderable Per MIL-STD-202, Method 208



BL3407
SOT-23



BL3407-3L
SOT-23-3L



Ordering Information

Part Number	Package	Shipping Quantity	Marking Code
BL3407	SOT-23	3000 pcs / Tape & Reel	3407
BL3407-3L	SOT-23-3L	3000 pcs / Tape & Reel	3407

Maximum Ratings (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter		Symbol	Value	Unit
Drain-Source Voltage		V _{DSS}	-30	V
Gate -Source Voltage		V _{GSS}	±20	V
Continuous Drain Current	T _A = 25°C *1	I _D	-4.3	A
	T _A = 70°C *1		-3.5	A
Pulsed Drain Current (t _p = 10μs, T _A = 25°C)		I _{DM}	-17	A
Single Pulse Avalanche Energy *3		E _{AS}	12	mJ
Power Dissipation	T _A = 25°C *1	P _D	1	W
	T _C = 25°C		1.8	W
Operating Junction Temperature Range		T _J	-55 ~ +150	°C
Storage Temperature Range		T _{STG}	-55 ~ +150	°C

Thermal Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit
Thermal Resistance Junction-to-Case ^{*1}	R _{θJC}	-	56	70	°C/W
Thermal Resistance Junction-to-Air ^{*1}	R _{θJA}	-	105	125	°C/W

Electrical Characteristics (@ T_A = 25°C unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
Static Characteristics						
V _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = -250μA	-30	-	-	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = -24V, V _{GS} = 0V	-	-	-1	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} = ±20V, V _{DS} = 0V	-	-	±100	nA
On Characteristics						
R _{DS(ON)}	Drain-Source On-resistance *2	V _{GS} = -10V, I _D = -4.1A	-	40	52	mΩ
		V _{GS} = -4.5V, I _D = -3A	-	59	87	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = -250μA	-1	-1.5	-2.1	V
R _G	Gate Resistance	V _{GS} = 0V, f = 1MHz	-	12	-	Ω
Dynamic Characteristics						
g _{FS}	Forward Transconductance	V _{DS} = -5V, I _D = -4A	-	7	-	S
C _{ISS}	Input Capacitance	V _{GS} = 0V V _{DS} = -15V f = 1.0MHz	-	793	-	pF
C _{OSS}	Output Capacitance		-	78	-	
C _{RSS}	Reverse Transfer Capacitance		-	61	-	
Switching Characteristics						
t _{d(ON)}	Turn-on Delay Time *4	V _{DD} = -15V, V _{GS} = -10V R _G = 2.5Ω, R _L = 15Ω I _D = -1A	-	5	-	ns
t _r	Turn-on Rise Time *4		-	6	-	
t _{d(OFF)}	Turn-Off Delay Time *4		-	28	-	
t _f	Turn-Off Fall Time *4		-	7	-	
Q _G	Total Gate-Charge	V _{DD} = -20V	-	8	-	nC
Q _{GS}	Gate to Source Charge	V _{GS} = -4.5V	-	2.6	-	
Q _{GD}	Gate to Drain (Miller) Charge	I _D = -3A	-	2.6	-	
Source-Drain Diode Characteristics						
V _{SD}	Diode Forward Voltage *2	I _{SD} = -1A, V _{GS} = 0V, T _J = 25°C	-	-0.8	-1.0	V
t _{rr}	Reverse Recovery Time	I _{SD} = -3A, V _{GS} = 0V	-	125	-	ns
Q _{rr}	Reverse Recovery Charge	dI/dt = 100A/μs	-	110	-	nC

Notes:

1. The data tested by surface mounted on a 1 inch² FR-4 board with 20Z copper
2. The data tested by pulsed, pulse width ≤ 300μs, duty cycle ≤ 2%
3. The E_{AS} data shows Max. rating. The test condition is V_{DD} = -15V, V_{GS} = -10V, L = 0.1mH
4. Guaranteed by design, not subject to production

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Typical Output Characteristics




Fig 2 On-Resistance vs. Drain Current
and Gate Voltage




Fig 3 On-Resistance vs. Gate-Source Voltage




Fig 4 Body-Diode Characteristics




Fig 5 Normalized On-Resistance vs. Junction
Temperature




Fig 6 Transfer Characteristics




Fig 7 Capacitance Characteristics




Fig 8 Gate-Charge Characteristics




Fig 9 Normalized Breakdown Voltage
vs. Junction Temperature




Fig 10 Normalized $V_{GS(th)}$ vs. Junction Temperature




Fig 11 Safe Operation Area






Fig 12 Normalized Maximum transient thermal
impedance

Package Outline Dimensions (Unit: mm)




SOT-23		
Dimension	Min.	Max.
A	2.70	3.10
B	1.10	1.50
C	0.90	1.10
D	0.30	0.50
E	0.35	0.48
G	1.80	2.00
H	0.02	0.10
J	0.05	0.15
K	2.20	2.60




SOT-23-3L		
Dimension	Min.	Max.
A	2.80	3.00
B	1.50	1.70
C	1.00	1.20
D	0.35	0.45
E	0.35	0.55
G	1.80	2.00
H	0.02	0.10
J	0.10	0.20
K	2.60	3.00

Package Outline Dimensions (Unit: mm)

SOT-23



SOT-23-3L



IMPORTANT NOTICE

Galaxy Microelectronics (GME) reserves the right to make changes without further notice to any product herein to make corrections, modifications, improvements, or other changes. GME does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others.