




COIL: @ 25°C

RESISTANCE 330 OHMS $\pm$ 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.0 VDC

MUST RELEASE 2.0 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C


NOTES: OPERATE TIME 13 MS MAX.

RELEASE TIME 5 MS MAX.

CONTACT BOUNCE 5 MS MAX. (NC)

2 MS MAX. (NO)

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMPS 30 VDC RES.
10 AMPS 115 VAC 400 Hz, 6A 30 VDC
INDUCTIVE 100,000 OPERATIONS

DR. R.B. 11/15/93 CK. 11/15/93

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. HI-G
CUST. NO. 2T-2A-126

TYPE "07" RELAY

B07B035BZ1-8013