

## **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-3YH50-0CF0

Client order no. : Order no. : Offer no. : Remarks :

Rated data			
Input			
	Number of phases	3 AC	
ı	Line voltage	500 690 V +10 % -20 %	
1	Line frequency	47 63 Hz	
ı	Rated voltage	690V IEC	600V NEC
	Rated current (LO)	171.00 A	171.00 A
	Rated current (HO)	158.20 A	158.20 A
Output			
	Number of phases	3 AC	
-	Rated voltage	690V IEC	600V NEC 1)
	Rated power (LO)	160.00 kW	150.00 hp
	Rated power (HO)	132.00 kW	150.00 hp
	Rated current (LO)	171.00 A	171.00 A
	Rated current (HO)	144.00 A	144.00 A
	Rated current (IN)	175.00 A	
	Max. output current	231.00 A	
Pulse frequency		2 kHz	
Output frequency for vector control		0 200 Hz	
Output frequency for V/f control		0 550 Hz	
Overload capability			

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

 $150\%\,x$  base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor $\lambda$	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	74 dB	
Power loss 3)	2.930 kW	
Filter class (integrated)	RFI suppression filter for Category C3	
EMC category (with accessories)	Category C3	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	

Communication

Communication PROFINET, EtherNet/IP



Item no. : Consignment no. : Project :

	Inputs / outputs			
S	Standard digital inputs			
	Number	6		
	Switching level: $0 \rightarrow 1$	11 V		
	Switching level: $1 \rightarrow 0$	5 V		
	Max. inrush current	15 mA		
F	Fail-safe digital inputs			
	Number	1		
D	Digital outputs			
	Number as relay changeover contact	2		
	Output (resistive load)	DC 30 V, 5.0 A		
	Number as transistor	0		
A	Analog / digital inputs			
	Number	2 (Differential input)		

9	Switching threshold as digital input		
	0 → 1	4 V	
	1 → 0	1.6 V	
,	Analog outputs		

10 bit

1 (Non-isolated output)

## PTC/ KTY interface

Number

Resolution

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy  $\pm 5\,^{\circ}\text{C}$ 

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	



## **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-3YH50-0CF0


Standard board coating type			
	Class 3C2, according to IEC 60721-3-3: 2002		
Cooling	Air cooling using an integrated fan		
Cooling air requirement	0.210 m³/s (7.416 ft³/s)		
Installation altitude	1,000 m (3,280.84 ft)		
Ambient temperature			
Operation	-20 45 °C (-4 113 °F)		
Transport	-40 70 °C (-40 158 °F)		
Storage	-25 55 °C (-13 131 °F)		
Relative humidity			
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible		
Connections			
Signal cable			
Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)		
Line side			
Version	M10 screw		
Version  Conductor cross-section	M10 screw 35.00 2 x 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)		
	35.00 2 x 185.00 mm <sup>2</sup>		
Conductor cross-section	35.00 2 x 185.00 mm <sup>2</sup>		
Conductor cross-section  Motor end	35.00 2 x 185.00 mm² (AWG 1 MCM 2 x 350)		
Conductor cross-section  Motor end  Version	35.00 2 x 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)  M10 screw  35.00 2 x 185.00 mm <sup>2</sup>		
Conductor cross-section  Motor end  Version  Conductor cross-section	35.00 2 x 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)  M10 screw  35.00 2 x 185.00 mm <sup>2</sup>		
Conductor cross-section  Motor end  Version  Conductor cross-section  DC link (for braking resistor)	35.00 2 x 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)  M10 screw  35.00 2 x 185.00 mm <sup>2</sup> (AWG 1 MCM 2 x 350)		

Mechanical data			
Degree of protection	IP20 / UL open type		
Frame size	FSG		
Net weight	105 kg (231.49 lb)		
Dimensions			
Width	305 mm (12.01 in)		
Height	999 mm (39.33 in)		
Depth	369 mm (14.53 in)		
Standards			
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH		
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		

Converter losses to IEC61800-9-2\*

IE2

35.2 %



The percentage values show the losses in relation to the rated apparent power of the converter.

50%

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

Efficiency class

Comparison with the reference

converter (90% / 100%)

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 550V-600V

<sup>&</sup>lt;sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



## **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-3YH50-0CF0

	Operator panel: I	ntelligent Operator Panel (IOP-2
	Screen	
Display design	LCD color	Ambient temperature
Screen resolution	320 x 240 Pixel	Operation
	Storage	
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.134 kg (0.30 lb)	Relative humidity at 25
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	shi operation
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	Certificate of suitability

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
	55 °C only with door installation kit	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Ammuniala		
	Approvals	
Certificate of suitability CE, cULus, EAC, KCC, RCM		