

## CYW20736A1KML2GT

Status: In Production

## CYW20736A1KML2GT

Automotive Grade	No
Automotive Qualified	N
Bluetooth Specification	Bluetooth 4.1
CPU Core	ARM Cortex M3
Cypress Module Area (mm)	N/A
Dedicated ADC (Max. Resolution @ Sampling Rate)	10-bit @ 187 KHz (Static) 13-bit @ 5.8 KHz (Audio)
Device Type	Silicon
Interfaces	2 UART, 2 SPI, I2C
Max. Operating Frequency (MHz)	24
Max. Operating Temp. (°C)	85
Max. Operating Voltage (V)	3.60
Min. Operating Temp. (°C)	-30
Min. Operating Voltage (V)	1.40
Module Features	N/A
No. of Dedicated Timer/Counter/PWM Blocks	4
No. of GPIOs	14
Partner Modules Available	Y
Power-Class	Class 2, Class 3
Product Family	BCM20736
RAM (KB)	60
Silicon Features	Infrared TX/RX, Wireless Charging (A4WP), LE Audio
Software Support	WICED
Tape & Reel	Y
Wireless Technology	Bluetooth Low Energy

Package Carrier	REEL
Package Carrier Drawing / Orientation	<a href="#">Package Orientation</a>
Standard Pack Quantity	2500
Minimum Order Quantity (MOQ)	2500
Order Increment	2500
HTS Code	8542.31.0000
ECCN	None
ECCN Suball	5A992C

## QUALITY AND ROHS

Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	<a href="#">Y Print RoHS Certificate of Compliance</a>
PB Free	Y
Lead/Ball Finish	Pure Sn
Marking	<a href="#">Cypress Marking Format</a>